




REVISIONS				
P	LTN	DESCRIPTION	DATE	APP'D
S		REVISED PER ECO-15-008006	17NOV2015	NK MM
T		RESIN CHANGE (LOW TEMP RESIN TO HIGH TEMP RESIN)	03JUL2025	RS GVP
T1		ECR-25-263516	01DEC2025	ABS PS



- △ HOUSING: GLASS FILLED THERMOPLASTIC, UL 94-VO RATED, COLOR: BLACK
CONTACTS: COPPER ALLOY PER ASTM B103
- △ MOLDED CIRCUIT #1 IDENTIFIER IN LOCATION SHOWN.
- △ 0.000761(.000030) MIN. GOLD IN CONTACT AREA, 0.00127-0.00254(.000050-.000100) TIN-LEAD IN AREA E, ALL OVER 0.00127(.000050) MIN. NICKEL.
- △ 0.000761(.000030) MIN. GOLD IN CONTACT AREA, 0.00127 - 0.00254 (.000050-.000100) TIN IN AREA E, ALL OVER 0.00127(.000050) MIN. NICKEL.
- 5 USE WITH #20-#22 AWG WIRE SIZE, .050 MAX INSULATION DIA., .015 MAX INSULATION WALL THICKNESS.
- △ CONTACT IDENTIFICATION NUMBER "3" LOCATED IN THIS AREA.
- △ TE LOGO ON EITHER SIDE.
- △ OBSOLETE PART NUMBER.
- △ ROHS 2002/95/EC COMPLIANT.
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

△/△	81.28 [3.200]	31	64	8-102448-0	△
△/△	76.20 [3.000]	29	60	7-102448-8	△
△/△	68.58 [2.700]	26	54	7-102448-5	△
△/△	63.50 [2.500]	24	50	7-102448-3	△
△/△	50.80 [2.000]	19	40	6-102448-8	△
△/△	43.18 [1.700]	16	34	6-102448-5	△
△/△	40.64 [1.600]	15	32	6-102448-4	△
△/△	38.10 [1.500]	14	30	6-102448-3	△
△/△	35.56 [1.400]	13	28	6-102448-2	△
△/△	33.02 [1.300]	12	26	6-102448-1	△
△/△	30.48 [1.200]	11	24	6-102448-0	△
△/△	27.94 [1.100]	10	22	5-102448-9	△
△/△	25.40 [1.000]	9	20	5-102448-8	△
△/△	22.86 [.900]	8	18	5-102448-7	△
△/△	20.32 [.800]	7	16	5-102448-6	△
△/△	17.78 [.700]	6	14	5-102448-5	△
△/△	15.24 [.600]	5	12	5-102448-4	△
△/△	12.70 [.500]	4	10	5-102448-3	△
△/△	10.16 [.400]	3	8	5-102448-2	△
△/△	7.62 [.300]	2	6	5-102448-1	△
FINISH	B	A	NO OF POS	ASSEMBLY PART NUMBER	

△	91.44 [3.600]	35	72	△ 3-102448-4
△	88.90 [3.500]	34	70	△ 3-102448-3
△	86.36 [3.400]	33	68	△ 3-102448-2
△	83.82 [3.300]	32	66	△ 3-102448-1
△	81.28 [3.200]	31	64	3-102448-0
△	78.74 [3.100]	30	62	△ 2-102448-9
△	76.20 [3.000]	29	60	2-102448-8
△	73.66 [2.900]	28	58	△ 2-102448-7
△	71.12 [2.800]	27	56	△ 2-102448-6
△	68.58 [2.700]	26	54	2-102448-5
△	66.04 [2.600]	25	52	2-102448-4
△	63.50 [2.500]	24	50	2-102448-3
△	60.96 [2.400]	23	48	△ 2-102448-2
△	58.42 [2.300]	22	46	△ 2-102448-1
△	55.88 [2.200]	21	44	△ 2-102448-0
△	53.34 [2.100]	20	42	△ 1-102448-9
△	50.80 [2.000]	19	40	1-102448-8
△	48.26 [1.900]	18	38	△ 1-102448-7
△	45.72 [1.800]	17	36	△ 1-102448-6
△	43.18 [1.700]	16	34	△ 1-102448-5
△	40.64 [1.600]	15	32	1-102448-4
△	38.10 [1.500]	14	30	△ 1-102448-3
△	35.56 [1.400]	13	28	1-102448-2
△	33.02 [1.300]	12	26	1-102448-1
△	30.48 [1.200]	11	24	1-102448-0
△	27.94 [1.100]	10	22	△ 102448-9
△	25.40 [1.000]	9	20	△ 102448-8
△	22.86 [.900]	8	18	102448-7
△	20.32 [.800]	7	16	102448-6
△	17.78 [.700]	6	14	102448-5
△	15.24 [.600]	5	12	102448-4
△	12.70 [.500]	4	10	102448-3
△	10.16 [.400]	3	8	△ 102448-2
△	7.62 [.300]	2	6	102448-1
FINISH	B	A	NO. OF POS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

OWNER: S. SHUEY 30DEC91
CHK: M. RIDER 06JAN92
APP'D: R. FELIX 07JAN92

DIMENSIONS: mm [INCHES]
TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL: SEE TABLE

WEIGHT: 114-25032
SCALE: 5:1

NAME: AMPMODU MT. RCPT ASSY. STANDARD PRESSURE CONTACTS FOR 20-22 AWG WIRE SIZE

SIZE: 108-25015
APPLICATION SPEC: 114-25032

RESTRICTED TO: A | 00779 | C=102448

CUSTOMER DRAWING

TE Connectivity