




COIL: $\bullet$ +25 °C

RESISTANCE 700 OHMS $\pm$ 10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 13.5 VDC

MUST RELEASE 8.0 VDC MAX, 1.5 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS $\bullet$ 30 g's

SHOCK 100 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C


NOTES: OPERATE 4 MS MAX

RELEASE 4 MS MAX

CONTACT STABILIZATION TIME 2.5 MS MAX

ALL OTHER REQUIREMENTS TO M39016/6-209M

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
2 AMPS 28 VDC RESISTIVE 100,000
OPERATIONS

DR. R.B. 11/19/93 CK. 11/19/93 gms

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. OPL

CUST. NO. M39016/6-209M

TYPE "HFW" RELAY

HFW1201K46M