




11	OBSOLETE	10	2	2.40	1.198	1-103648-1	12	6-103970-1
11	OBSOLETE	10	2	2.20	1.098	1-103648-0	11	6-103970-0
11	OBSOLETE	10	2	2.00	0.998	103648-9	10	5-103970-9
11	OBSOLETE	10	2	1.80	0.898	103648-8	9	5-103970-8
11	OBSOLETE	10	2	1.60	0.798	103648-7	8	5-103970-7
11	OBSOLETE	10	2	1.40	0.698	103648-6	7	5-103970-6
11	OBSOLETE	10	4	2.39	0.598	103648-5	6	5-103970-5
11	OBSOLETE	10	4	1.99	0.498	103648-4	5	5-103970-4
	OBSOLETE	10	5	1.99	0.398	103648-3	4	5-103970-3
	OBSOLETE	10	8	2.40	0.298	103648-2	3	5-103970-2
		10	10	2.00	0.198	103648-1	2	5-103970-1
11	OBSOLETE	9	2	2.40	1.198	1-103648-1	12	1-103970-1
11	OBSOLETE	9	2	2.20	1.098	1-103648-0	11	1-103970-0
11	OBSOLETE	9	2	2.00	0.998	103648-9	10	103970-9
11	OBSOLETE	9	2	1.80	0.898	103648-8	9	103970-8
11	OBSOLETE	9	2	1.60	0.798	103648-7	8	103970-7
11	OBSOLETE	9	2	1.40	0.698	103648-6	7	103970-6
11	OBSOLETE	9	4	2.39	0.598	103648-5	6	103970-5
	OBSOLETE	9	4	1.99	0.498	103648-4	5	103970-4
SUPERSEDED BY 5-103970-3			9	5	1.99	0.398	4	103970-3
	OBSOLETE	9	8	2.40	0.298	103648-2	3	103970-2
		9	10	2.00	0.198	103648-1	2	103970-1
			6	B	A	HOUSING PART NUMBER 1 REQD	NO OF POSN PER ASSY	ASSEMBLY PART NUMBER ON STRIP

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN L. MAYER 05 NOV 1986		TE TE Connectivity						
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK P.C.DEJONG 12-11-86								
		0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH		APVD 12-11-86		NAME RCPT ASSY, AMPMODU MTE, SINGLE ROW, .100 CL WITH GUIDE RIBS, FOR #22-#26 AWG WIRE SIZE, STRIP FORM						
				PRODUCT SPEC								
				APPLICATION SPEC								
				MATERIALS: FLAME RETARDANT THERMOPLASTIC, COLOR:BLACK CONTACTS: PHOS BRONZE		SEE TABLE		114-25026		SIZE A2	CAGE CODE 00779	DRAWING NO C-103970
				WEIGHT -		CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 1	REV H2