




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A		NEW DRAWING	31 JUL 2024	AN	JC


GENERAL TOLERANCES:  
 LINEAR:  $\pm 0.8$   
 HOLE CENTRES:  $\pm 0.5$   
 ANGULAR:  $\pm 0.5^\circ$



4 X Ø5 THRU ALL  
 $\sqrt{08.30 \times 90^\circ}$

4 X NICKEL/COPPER FABRIC  
 CONDUCTIVE STRIP

1 LAYER 3.18 CELL X 6.35 THK  
 ALUMINIUM 5052 HONEYCOMB  
 SURTEC 650 FINISH



THE VENT BODY DESIGN  
 & OBSTRUCTED AREA  
 MAY VARY

ISOMETRIC VIEW (NTS)

HIGH IMPACT ABS	KEMVENT70	2489075-1
MATERIAL	ALIAS PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm .1$ 1 PLC $\pm 0.1$ 2 PLC $\pm 0.01$ 3 PLC $\pm 0.001$ 4 PLC $\pm 0.0001$ ANGLES $\pm$ FINISH -	DWN 31 JUL 2024 AYESHABANU N CHK 31 JUL 2024 SELVAPANDIAN B APVD 31 JUL 2024 JAMES CAVILL	NAME KEM_1651-KEMVENT_70
MATERIAL SEE TABLE	FINISH -	PRODUCT SPEC -	APPLICATION SPEC -
		WEIGHT -	SIZE A2
		CUSTOMER DRAWING	SCALE 2:1 SHEET 1 OF 1 REV A

TE Connectivity