




CUSTOMER DATA SHEET

COIL: @ +25°C 26.5VDC NOMINAL

TOLERANCE UNLESS OTHERWISE SPECIFIED
DECIMALS ±.005 FRACTIONAL ± 1/64

WINDING # 1

WINDING # 2

675 OHMS

OHMS

13.5V MUST OPERATE

MUST OPERATE

26.5 VDC NOMINAL


ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 100 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 5MS MAX
CONTACT BOUNCE 1MS MAX



CONTACT RATING: LOW LEVEL TO
2 AMPS @ 28 VDC RESISTIVE
100,000 OPERATIONS.

DR. 4-16-85

CK. OSW



Communications
Instruments, Inc.

CUST. QPL

CUST. NO. M5757/10-035

TYPE "FW" RELAY

FW 1109G06