

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	NEW DRAWING CREATED IN CREO	03FEB2015	JB JH	BRUN
	C2	LEAD REMOVED AT NOTE 2	18NOV2015	MAH.	BRUN
	C3	REVISED PER ECR-23-194738	14AUG2025	RK	DJ

17.7 MAX.

14 MAX.
FOR LOOSE PIECE

3.3

Ø1.52

A

B

0.15 max.

NOTES:

1 SUITABLE FOR 0.64 x 0.64 POST

2 CRIMP AREA PLATED WITH 2.5 µm MIN. TIN OVER 0.8 NICKEL

3 GOLD PLATING

- 2 0.4 µm GOLD OVER 0.8 µm NICKEL
- 3 0.8 µm GOLD OVER 0.8 µm NICKEL
- 4 1.25 µm GOLD OVER 0.8 µm NICKEL
- 5 2.0 µm GOLD OVER 0.8 µm NICKEL
- 1- -5 1.5 µm GOLD OVER 1.25 µm NICKEL
- 1- -6 1 µm GOLD OVER 1.25 µm NICKEL
- 8 1.7 µm GOLD OVER 0.8 µm NICKEL

4 POST STOP DIMENSION

4.4

1.5

7.0 MIN.
CRIMP AREA

1.07

1.74

SECTION A-A

0.23

1.73

SECTION B-B

	215141-8	PHOSPHER BRONZE	2 3
	1-215141-6		
OBSOLETE	4-215141-5		
	215141-5		
OBSOLETE	215141-4		
	215141-3		
OBSOLETE	215141-2		
	ORDER NO.	MATERIAL	PLATING

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 03FEB1986

CHK 05FEB1986

APVD 17FEB1986

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

±

±

±

±

±

±

-

-

NAME

RECEPTICAL CONTACT WITH

MASS TERMINATION AREA FOR AWG 26-22

-

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

SCALE

SHEET

REV

TE Connectivity

A3

-

C=215141

10:1

1 OF 1

C3

1470-19 (3/13)