


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
020	ECN 92-0591-2	2/1/93	BB 2/3/93



			HOUSING CAP	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303		GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290		
ELECTRICAL			DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457		N/A		
MECHANICAL			CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H		GOLD PLATE PER MIL-G-45204 OVER COPPER PLATE PER MIL-C-14550		
ENVIRONMENTAL			COMPONENT	MATERIAL		FINISH		
Nominal Impedance (Ohms) 50 Frequency Range (GHz) DC to 18 Volt Rating (VRMS MAX) Ø Sea Level 250 VSWR N/A Insertion Loss (dB MAX) N/A RF Leakage (dB MIN) N/A Corona, 70,000 Ft (VRMS MIN) 190 Dielectric Withstanding Voltage (VRMS MIN) Ø Sea Level 750 Contact Resistance (Milliohms MAX) Center Contact 2.0 Outer Contact 2.0 RF High Potential Ø Sea Level (VRMS MIN Ø 5 MHz) 500 I.R.(Megohms MIN) 5000			UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°		DRAWN BY EJC DATE 12/1/71			
			CHECKED BY PRB 12/6/71		AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599			
			APPD BY RW 12/6/71		AMP			
Interface Dimensions MIL-STD-348A, Fig. 319.2 Recommended Mating Torque 7 to 8 In-Lbs Mating Characteristics: Insertion (MAX Lbs) 3 Withdrawal (MIN Oz) 1 Force to Engage and Disengage (In-Lbs MAX) 2 Center Contact Captivation Axial (Lbs) 6 Radial (In-Oz) 4 Weight (Grams) TBD			These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.		TITLE OSSM RIGHT ANGLE PRINTED WIRING BOARD JACK STRAIGHT TERMINAL			
					SIZE B		CODE IDENT NO. 26805	REV 020
					SCALE 4:1		SHEET 1 OF 1	
Temperature Rating -55°C to +125°C Vibration MIL-STD-202, Method 204, Condition D Shock MIL-STD-202, Method 213, Condition I Thermal Shock MIL-STD-202, Method 107, Condition B, Except High Temp Shall Be +115°C Moisture Resistance MIL-STD-202, Method 106 Corrosion - MIL-STD-202, Method 106, No Measurements at High Humidity			USE ASS'Y PROCEDURE		1064-0000-00			
			NO. A.P. N/A					