



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H4	REVISED PER ECR-25-251256	17FEB2026	LP	MFP




NOTES

- 1 ASTERISK * FOR PH.BRONZE VERSIONS ONLY.
- 2 WIRE RANGE: 1,0-2,6mm². INSUL. RANGE: 4,3mm MAX. DIA..
- 3 OBSOLETE WITHOUT REPLACEMENT



TAPE MOUNTED	1	GOLDPLATED	PH.BRONZE	5-160313-7 3
	1	SILVERPLATED	PH.BRONZE	5-160313-6 3
	1	TINPLATED	PH.BRONZE	5-160313-5 3
		GOLDPLATED	BRASS	5-160313-4 3
		SILVERPLATED	BRASS	5-160313-3 3
		TINPLATED	BRASS	5-160313-2 3
LOOSE PIECE	1	TIN-LEAD	PH.BRONZE	9-160313-8 3
	1	GOLDPLATED	PH.BRONZE	9-160313-7 3
	1	SILVERPLATED	PH.BRONZE	9-160313-6
	1	TINPLATED	PH.BRONZE	9-160313-5
		GOLDPLATED	BRASS	9-160313-4 3
		SILVERPLATED	BRASS	9-160313-3 3
		TINPLATED	BRASS	9-160313-2
PACKAGE TYPE		FINISH	MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 08OCT04	 TE Connectivity		
		CHK T MICHELUTTI 08OCT04			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T MICHELUTTI 08OCT04	NAME		
	0 PLC ± -	PRODUCT SPEC	.250 SRS P.I.D.G. FASTON REC.		
	1 PLC ± -	APPLICATION SPEC			
MATERIAL	2 PLC ± 0.38	WEIGHT	SIZE	CAGE CODE	DRAWING NO
	3 PLC ± -		A3	00779	C-160313
	4 PLC ± -	CUSTOMER DRAWING		SCALE	SHEET
	ANGLES ± -			—	1 of 1
	FINISH			REV	H4