









- ⚠ MATERIAL: COPPER ALLOY C511.
- ⚠ FINISH: PRE-PLATED WITH 1.00µm MIN BRIGHT TIN.
- ⚠ MATERIAL ID FEATURE IN "DOWN" POSITION.
4. THE INTENDED TEMPERATURE RANGE FOR THIS TERMINAL IS -40°C TO +100°C.
5. TERMINAL HAS NYE LUBRICANTS NYETACT 568J-50-UV PERFORMANCE LUBE/GREASE APPLIED. THIS IS A WHITISH COLORED LUBE. AMOUNT AND VISIBILITY MAY VARY.
- ⚠ NOT FOR SEALED APPLICATIONS.
- ⚠ SEALING CAPABILITY MUST BE VALIDATED ON AN APPLICATION BASIS.
- ⚠ MATERIAL: COPPER ALLOY C425.



PART NUMBERS - SEE SHEET 2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL	01JUL2008	 TE Connectivity	
		CHK C. SCHMID	01JUL2008		
		APVD C. SCHMID	01JUL2008		
		NAME			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CONTACT, FEMALE, 0.64, GENERATION Y SEALED APPLICATIONS	
mm		0 PLC ± 1 PLC ± 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ± FINISH		SIZE CAGE CODE DRAWING NO	
		PRODUCT SPEC 108-2296 APPLICATION SPEC 114-13183		RESTRICTED TO	
MATERIAL		WEIGHT		A100779C=2035334	
SEE TABLE		SEE TABLE		CUSTOMER DRAWING	
				SCALE 15:1	SHEET 1 OF 2 REV C1

REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

0.13 = 0.85 - 1.05; 0.35 = 1.10 - 1.40	DETAIL B	1.40	2.40	0.80	1.85			2x 0.13mm ²	2-2035334-8
								0.35mm ²	
0.85 - 1.05	DETAIL B	0.85	1.82	0.65	1.50			26 [0.13mm ²]	2-2035334-7
0.13 = 0.85 - 1.05; 0.35 = 1.10 - 1.40	DETAIL A	1.40	2.40	0.80	1.85			2x 0.13mm ²	2-2035334-6
								0.35mm ²	
0.85 - 1.05	DETAIL A	0.85	1.82	0.65	1.50			26 [0.13mm ²]	2-2035334-5
2.06 MAX	DETAIL B	1.78	2.94	1.00	1.96			18 [0.75mm ²]	2-2035334-4
1.5 - 1.85	DETAIL B	1.78	2.94	0.80	1.82			20-22 [0.50-0.35mm ²]	2-2035334-3
2.06 MAX	DETAIL A	1.78	2.94	1.00	1.96			18 [0.75mm ²]	2-2035334-2
1.5 - 1.85	DETAIL A	1.78	2.94	0.80	1.82			20-22 [0.50-0.35mm ²]	2-2035334-1
0.13 = 0.85 - 1.05; 0.35 = 1.10 - 1.40	DETAIL B	1.40	2.40	0.80	1.85			2x 0.13mm ²	2035334-8
								0.35mm ²	
0.85 - 1.05	DETAIL B	0.85	1.82	0.65	1.50			26 [0.13mm ²]	2035334-7
0.13 = 0.85 - 1.05; 0.35 = 1.10 - 1.40	DETAIL A	1.40	2.40	0.80	1.85			2x 0.13mm ²	2035334-6
								0.35mm ²	
0.85 - 1.05	DETAIL A	0.85	1.82	0.65	1.50			26 [0.13mm ²]	2035334-5
2.06 MAX	DETAIL B	1.78	2.94	1.00	1.96			18 [0.75mm ²]	2035334-4
1.5 - 1.85	DETAIL B	1.78	2.94	0.80	1.82			20-22 [0.50-0.35mm ²]	2035334-3
2.06 MAX	DETAIL A	1.78	2.94	1.00	1.96			18 [0.75mm ²]	2035334-2
1.5 - 1.85	DETAIL A	1.78	2.94	0.80	1.82			20-22 [0.50-0.35mm ²]	2035334-1
INSULATION DIAMETER	REELING	M	L	K	J	FINISH	MATERIAL	WIRE SIZE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

-

SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.15
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

SEE TABLE

DWN R. VESTAL 01JUL2008
CHK C. SCHMID 01JUL2008
APVD C. SCHMID 01JUL2008

PRODUCT SPEC 108-2296
APPLICATION SPEC 114-13183
WEIGHT -

CUSTOMER DRAWING

NAME CONTACT, FEMALE, 0.64, GENERATION Y SEALED APPLICATIONS
SIZE A1
CAGE CODE 00779
DRAWING NO 2035334

RESTRICTED TO -

SCALE 15:1
SHEET 2 OF 2
REV C

TE Connectivity

4805 (3/13)