





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
		C		REV PER ECO 14-018159	12-15-14	CT
		D		REVISED PER ECO-16-002176	30MAR2016	RS



RECOMMENDED PC BOARD LAYOUT
COMPONENT SIDE SHOWN
SCALE 10:1



- 1 MATERIAL:
CONTACT - COPPER ALLOY
HOUSING - LCP, COLOR - BLACK
- 2 FINISH:
MATING AREA: 0.76µm MIN GOLD OVER
1.27µm MIN NICKEL
COMPLIANT PIN AREA: 2.54µm MIN MATTE TIN
- 3 DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- 4 PCB - ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 5 REFERENCE APPLICATION SPEC 114-13251 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 6 REFERENCE PRINT 2102428 FOR DIMENSIONS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. BELACK	10MAR2011	 TE Connectivity	
DIMENSIONS:		CHK K. THACKSTON	-		
mm		APVD M. McALONIS	-	NAME HIGH POWER, METAL SHELL LRU, VERTICAL SOCKET MODULE	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
		0 PLC ±.13 1 PLC ±0.13 2 PLC ±0.10 3 PLC ±. 4 PLC ±. ANGLES ±2° FINISH SEE TABLE		APPLICATION SPEC	
MATERIAL		114-13251		SIZE CAGE CODE DRAWING NO	
		WEIGHT ~ 4.93 g		A100779C=2102442	
		CUSTOMER DRAWING		RESTRICTED TO	
				SCALE 8:1	
				SHEET 1 OF 1	
				REV D	