

LOC	DIST	REVISIONS				
HB	—	P	LTR	DESCRIPTION	DATE	APVD
			F	REMOVED THE RIB ON THE BASE TO CASE ECO-15-011310	3-Nov-15	YS.HHL.C
			F1	ADD NEW PN ECO-18-008228	25-May-18	WQ.Y K.T







Diagram dimension	Tolerance
0.99mm max.	±0.1mm
1 - 2.99mm	±0.2mm
3mm min.	±0.3mm



CONNECTION FIGURE





FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING (BOTTOM VIEW)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	H.SASAKI	STE TE Connectivity		
		CHK	Y.OIKAWA			
		APVD	A.NAGAI	NAME		
		PRODUCT SPEC		OJ-SS-HM CUSTOMER DRAWING		
		APPLICATION SPEC		—		
		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		WEIGHT	0	A300779	C-1461077	—
CUSTOMER DRAWING		SCALE	5:1	SHEET	1 OF 2	REV F1


LOC	DIST	REVISIONS				
HB	—	P	LTR	DESCRIPTION	DATE	APVD
			—	SEE SHEET 1	—	—

F1	1-1461077-4	OJ-SS-105HM	107-79010	5V	OJ-SS-105HM	i
	1461077-6	OJ-SS-148HM	107-79010	48V	OJ-SS-148HM	h
	1440007-2	OJ-SS-124HM	107-79010	24V	OJ-SS-124HM	g
	1461077-5	OJ-SS-118HM	107-79010	18V	OJ-SS-118HM	f
	1419135-3	OJ-SS-112HM	107-79010	12V	OJ-SS-112HM	e
	1461077-4	OJ-SS-109HM	107-79010	9V	OJ-SS-109HM	d
	1461077-3	OJ-SS-106HM	107-79010	6V	OJ-SS-106HM	c
	1461077-2	OJ-SS-105HM	107-79010	5V	OJ-SS-105HM	b
	1461077-1	OJ-SS-103HM	107-79010	3V	OJ-SS-103HM	a
	TE PART NO	TE TYPE NAME	PACKAGE SPEC	PART B	PART A	TYPE

RELAY TYPE


NOTE:

1.LOT NO. SYSTEM AS FOLLOWING:




- 2.TERMINAL DIMENSION IS BEFORE SOLDER DIP;
3.FOR THE TIN-PLATING OF THE PINS:
+0.1mm FOR WIDTH,THICKENSS AND DIAMETER.
+0.5mm FOR LENGTH.
4.MARKING FROM INK TO LASER AND USING WELDED CONTACT

5.ADD LOT NO. SYSTEM AS FOLLOWING;



- I, DIGITS FOR DAY OF THE WEEK
1...MONDAY IN THIS WEEK;
2...TUESDAY IN THIS WEEK;
.....
7...SUNDAY IN THIS WEEK
II, DIGITS FOR SHIFT OF THE DAY
1...DAY SHIFT IN THIS DAY;
2...NIGHT SHIFT IN THIS DAY;
III, ONE CHARACTER DISTINGUISH THE LINE IDENTITY,
SUCH AS: A,B.....Z

		EPOXY RESIN	SEAL (BASE & BOBBIN)	15
		3UEW	MAGNETIC WIRE	14
94V-0		P.B.T	CASE	13
94V-0		P.B.T	BASE	12
94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
94V-0		P.P.S	CARD	9
		Ag ALLOY	MOVABLE CONTACT	8
		Ag	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	PBP	NO.TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.SASAKI	TE Connectivity			
		CHK Y.OIKAWA				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	APVD A.NAGAI	NAME —			
		PRODUCT SPEC SEE SPEC TABLE	OJ-SS-HM CUSTOMER DRAWING			
		APPLICATION SPEC —	—			
		—	SIZE A3	CAGE CODE 00779	DRAWING NO C-1461077	RESTRICTED TO —
		WEIGHT 0				
MATERIAL —		FINISH —	CUSTOMER DRAWING			
		SCALE 5:1		SHEET 2 OF 2	REV F1	