




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D9	REVISED PER ECR-17-011424	9FEB2018	JH	PKS



- 1
- SPECIFICATIONS:
MAGNET WIRE #18 - #34 AWG, 1.02mm[.040] - 0.16mm[.006] DIA COPPER. LEAD WIRE #18 - #22 AWG, (0.8mm² - 0.3mm²) STRANDED, BONDED OR SOLID WITH PVC INSULATION. MAX. INSULATION O.D. 2.9mm[.115] NO STRIPPING REQUIRED. OTHER INSULATION TYPES, MAY BE ACCOMMODATED, CONSULT TYCO ELECTRONICS FOR APPROVAL.
- 2
- POCKET RECOMMENDATION:
#1601433 FOR DOUBLE BUSSED (COMMONED) TERMINALS AND #1601440 FOR TRIPLE BUSSED (COMMONED) TERMINAL.
- 3
- TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS SPECIFICATION 114-13166 FIGURE 3
- 4
- REDUCED PACKAGING QUANTITY.
- 5
- PRODUCT SPEC: STANDARD SIAMEZE 108-2085
HIGH TEMPERATURE 108-2293(1601046-3)
- 6
- PRELIMINARY - NOT FOR PRODUCTION.



UNPLATED	BRASS, SPRING HARD	331-101-000	8-1601046-1
POST TIN PLATED OVER NICKEL	BRASS, SPRING HARD	-	6-1601046-2
UNPLATED	BRASS, SPRING HARD	231-101-000	6-1601046-1
UNPLATED	BRASS, SPRING HARD	031-101-000	4-1601046-1
UNPLATED	BRASS, SPRING HARD	131-102-000	2-1601046-1
UNPLATED	BRASS, SPRING HARD	-	4 6 1-1601046-1
UNPLATED	EXTRA HARD Cu ALLOY	-	1601046-3
POST TIN PLATED OVER NICKEL	BRASS, SPRING HARD	-	1601046-2
UNPLATED	BRASS, SPRING HARD	131-101-000	1601046-1
FINISH	MATERIAL	REFERENCE PART NUMBER	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.13[.005]

3 PLC ± -

4 PLC ± -

ANGLES ± 2°

MATERIAL
BRASS, SPRING HARD

FINISH
SEE TABLE

DWN
J.WELLER
11JAN2002

CHK
M.FEHER
11JAN2002

APVD
K.RANDOLPH
11JAN2002

PRODUCT SPEC
-

5

APPLICATION SPEC
-

3

WEIGHT
0.0

CUSTOMER DRAWING

TE

TE Connectivity

NAME
STANDARD RANGE WIRE TO WIRE
HIGH CARRIER SIAMEZE TERMINAL

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1601046

RESTRICTED TO
-

SCALE
10:1

SHEET
1 OF 1

REV
D9

1471-9 (1/15)