


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P	REVISED PER ECR-26-271876	26MAR2026	MA	JFS

- 1 PART PACKAGED UNASSEMBLED.
- 2 CABLE CLAMPING AREA ADJUSTABLE FROM .010 TO .161 SQ IN BY REVERSING CLAMPING INSERTS. (2 INSERTS SUPPLIED)
- 3 CABLE CLAMPING AREA ADJUSTABLE FROM .010 TO .161 SQ IN BY CHANGING CLAMPING INSERTS. (4 INSERTS SUPPLIED, -4 ONLY)
- 4 .453 MAXIMUM CABLE OUTSIDE DIAMETER.
- 5 BULK PACKAGED KITS TO BE ORDERED IN MULTIPLES OF 200 ONLY.
- 6 NON-HEXAVALENT CHROMATE FINISH.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



6	INDIVIDUAL	1-206070-1
2 6	5 BULK	1-206070-0
2 6 7	OBSOLETE SMALL PACK	206070-9
2 6	INDIVIDUAL	206070-8
6 7	OBSOLETE INDIVIDUAL	206070-7
6 7	OBSOLETE SMALL PACK	206070-6
	OBSOLETE	5 BULK
	5 BULK	206070-4
6 2	SUPERSEDED BY 1-206070-0	5 BULK
6 2	SUPERSEDED BY 206070-8	INDIVIDUAL
	PACKAGING	PART NUMBER
		206070-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A GRAFF 4/23/91	TE Connectivity		
		CHK W.G.LENKER 7-22-92			
DIMENSIONS: INCHES		APVD -	NAME CABLE CLAMP KIT, STANDARD, SHELL SIZE 17, CPC		
		PRODUCT SPEC 108-10024			
		APPLICATION SPEC -			
MATERIAL THERMOPLASTIC		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-206070
		FINISH -	RESTRICTED TO -		
			SCALE NTS	SHEET 1 OF 1	REV P