


NOTES:
Tolerances cable lengths:
0m to 0.5m +30mm
0.5m to 1.0m +50mm
1.0m to 3.0m +100mm
< 3.0m +1.5%


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ECR-26-281790	09JUN2026	AP	RK



TECHNICAL DATA	
Operating voltage	max. 60 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Snap In
Protection	IP65

PUR CABLE	
No./diameter of wires	3 x 0.25 mm ²
Wire isolation	PP (br, bl, bk)
C-track properties	5 million
Jacket	PUR (UL/CSA)
Outer diameter	approx. 4.1 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-25...+80 °C

PVC CABLE	
No./diameter of wires	3 x 0.25 mm ²
Wire isolation	PVC (br, bl, bk)
C-track properties	
Jacket	PVC (UL/CSA)
Outer diameter	approx. 4.5 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	-30...+80 °C
Temperature range (mobile)	-5...+80 °C



OBSOLETE	3 pos	10mtr	PVC	Black	1-2273000-4	3x22AWG PVC 10.0m	8
5mtr		1-2273000-3			3x22AWG PVC 5.0m	7	
3mtr		1-2273000-2			3x22AWG PVC 3.0m	6	
1.5mtr		1-2273000-1			3x22AWG PVC 1.5m	5	
	3 pos	10mtr	PUR	Black	2273000-4	3x22AWG PUR 10.0m	4
		5mtr			2273000-3	3x22AWG PUR 5.0m	3
		3mtr			2273000-2	3x22AWG PUR 3.0m	2
		1.5mtr			2273000-1	3x22AWG PUR 1.5m	1
		LENGTH"L"	MATERIAL	JACKET COLOR	TE PN	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12NOV2013 SATHISH KUMAR .G	TE Connectivity				
		CHK 12NOV2013 B.VELDHOVEN					
DIMENSIONS: mm		APVD 12NOV2013 A.VAN ZANDVOORT	NAME M8 X 1.0 STRAIGHT PLUG PIGTAIL				
		PRODUCT SPEC 108-19483					
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APPLICATION SPEC 114-32127	SIZE A3		CAGE CODE 00779	DRAWING NO C-2273000	RESTRICTED TO -
		MATERIAL -	WEIGHT -		CUSTOMER DRAWING		
		FINISH -			SCALE NTS	SHEET 1 of 1	REV A2