






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D6	ECR-23-181044	12JUL2023	NR	DJ
	D7	ECR-23-181212	13JUL2023	NR	DJ
	D8	ECR-23-187176	15SEP2023	NR	DJ
	E	ECR-24-214941	14AUG2024	DK	DJ



SECTION B-B
SCALE 20:1



ISOMETRIC VIEW
SCALE 8:1



SECTION E-E
SCALE 20:1

- 1 MATERIAL: COPPER ALLOY, MATERIAL THICKNESS: 0.15mm
- 2 FINISH: 0.38 µm MIN GOLD PLATE AT MATING INTERFACE FLASH IN REST OF GOLD PLATE ZONE
1 µm - 3 µm TIN IN LOCALIZED TIN PLATE ZONE
ALL OVER 1.27 µm MIN NICKEL.

3. 2368031-1 AS SHOWN.
4. PACKAGED ON REEL.

DACAR 686-3, DACAR 585-3, G&G X9305, G&G X9534	2368031-1
APPLICABLE CABLE SIZE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N.SWANGER 02FEB2021	TE Connectivity			
DIMENSIONS: mm		CHK N.SWANGER 02FEB2021				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.HALL 02FEB2021	NAME CENTER CONTACT, PIN, 180 DEGREE, GEMNET			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC - APPLICATION SPEC 114-32334 WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-2368031	RESTRICTED TO -
MATERIAL 1		CUSTOMER DRAWING		SCALE 10:1	SHEET 1 OF 1	REV E