




REV. C
DCO 300783

TOLERANCES $\pm .010"$ - UNLESS
OTHERWISE SPECIFIED

COIL: @ 25°C
RESISTANCE _____ 500 OHMS $\pm 10\%$
NOMINAL VOLTAGE _____ 28 VDC
MUST OPERATE _____ 13.5 VDC MAX.
_____ TRANSIENT SUPPRESSION - 42 VDC MAX.
MUST RELEASE _____ 5.5 VDC MAX., 2.3 VDC MIN.


ENVIRONMENT:
VIBRATION _____ 70 Hz TO _____ 3000 Hz @ _____ 30 g's
SHOCK _____ 200 g's _____ 6 MS. DURATION
TEMPERATURE _____ -70 °C TO _____ +125 °C

NOTES: OPERATE, RELEASE 5 MS MAX.
CONTACT STABILIZATION 2.5 MS MAX.
CONTACT BOUNCE 1 MS MAX.
CONTACT BREAK BOUNCE 0.1 MS MAX.

CUST. _____ M83536/2-020M
CUST. NO. _____ REV. _____

TE NUMBER
4-1617758-5

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: _____ LOW LEVEL
TO 5 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE,
100,000 OPERATIONS

DR. B.D. 11MAR2008

CK. J.M.B. 3/17/08

Tyco Electronics

©COPYRIGHT 2005
TYCO ELECTRONICS CORPORATION
ALL INTERNATIONAL RIGHTS RESERVED

CII PART NUMBER
FCB-205-0220M