




P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	E-25-231556: PRODUCT IMPROVEMENT	08JAN2025	MF	PW
	D	ECR-25-238065: MATERIAL CHANGE	18FEB2025	MF	PW
	D1	ECR-25-264499: Note Change	04DEC2025	MF	PW
	E	ECN-26-382060 - New Lever	06MAY2026	MF	PW





AS SHOWN 2461722-1
CODING A 
Kodierung A




AS SHOWN 2461722-2
CODING B 
Kodierung B




AS SHOWN 2461722-3
CODING C 
Kodierung C




AS SHOWN 2461722-1




DELIVERY CONDITION:
Lieferzustand



LEVER IN LOCKED POSITION
Hebel in Verriegelungsstell



PRE-LOCKING POSITION:
Vorraststellung



NOTES

Bemerkungen,

- 1 TE-CONNECTIVITY ORDER-NUMBER
TE-Connectivity Bestellnummer
- 2 PRODUCTION DATE
Produktionsdatum
- 3 TE-LOGO
TE-Logo
- 4 MATERIAL MARKING
Materialkennzeichnung
- 5 CAVITY NUMBERING
Kammernummerierung
- 6 DIFFERENT CODINGS
Unterschiedliche Kodierungen
- 7 SUITABLE TO COUNTERPART PN 2461731
Passend zu Gegenstueck PN 2461731
- 8 DELIVERY CONDITION IN CLOSED POSITION
Lieferzustand in geschlossenem Zustand
- 9 MALFUNCTION CAUSED BY LACQUER IS NOT COVERED BY TE WARRANTY.
Funktionsbeeinträchtigung durch Lackieren liegt nicht im Einfluss und Gewährleistungsumfang von TE
- 10 PACKED INTERLAYERED IN CORRUGATED SHIPPING BOX
Verpackt in Lagen angeordnet im Versandkarton
- 11 NECESSARY ACCESSORIES BASED ON CABLE SIZE SEE FOLLOWING CUSTOMER DRAWINGS:
Notwendige Accessoires abhängig von der Kabelgröße, siehe folgende Kundenzeichnungen

TERMINAL POSITION ASSURANCE 2461739 and 2461740
Kontaktlagensicherung 2461739 and 2461740

CABLE SEAL 2461743
Kabeldichtung 2461743

COVER 2461742
Schutzhülle 2461742

STRAIN RELIEF 2461741
Zugentlastung 2461741

1	1	1	1	LEVER.1POS.PCON21.REC HSG.180° Hebel.1pol..PCON21. Buchsengeh.180°	PBT-GF30 FR	RED Rot	3
1	1	1	1	PERIPHERAL SEAL.PCON21 Radialdichtung.PCON21	SILICON	YELLOW Gelb	2
1	-	-	-	1POS.PCON21.REC HSG ASSY.SLD.COD D. 180° 1pol..PCON21.Buchsengeh.Assy.ged..COD D.180°	PBT-GF30 FR		1
-	1	-	-	1POS.PCON21.REC HSG ASSY.SLD.COD C. 180° 1pol..PCON21.Buchsengeh.Assy.ged..COD C.180°	PBT-GF30 FR		1
-	-	1	-	1POS.PCON21.REC HSG ASSY.SLD.COD B. 180° 1pol..PCON21.Buchsengeh.Assy.ged..COD B.180°	PBT-GF30 FR	EMERALD GREEN Smaragdgruen	1
-	-	-	1	1POS.PCON21.REC HSG ASSY.SLD.COD A. 180° 1pol..PCON21.Buchsengeh.Assy.ged..COD A.180°	PBT-GF30 FR	Black Schwarz	1
0-4	0-3	0-2	0-1	DESCRIPTION	MATERIAL	COLOUR	ITEM NO
-	-	D	D	REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)			
78.8	78.8	78.8	78.8	WEIGHT OF EACH ASSY NO [g]			
QTY REQD PER ASSY				PARTS LIST			

DIMENSION AND TOLERANCES ACCORDING TO:
Bemaßungen und Toleranzen gemäß:

DIN ISO 20457
DIN EN ISO 8015 (AD) - DIN EN ISO 291
DIN EN ISO 14405-1/-2/-3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. Floesser 14DEC2023		 TE Connectivity	
DIMENSIONS: mm		CHK P. Wrobel 14DEC2023			
		APVD F. Eltrop 15DEC2023		NAME 1POS.,PCON21,REC HSG ASSY,SLD,180DEG 1pol.,PCON21,Buchsengeh. Assy,ged.180grad -	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:			
		0 PLC ± 0.1 1 PLC ± 0.01 2 PLC ± 0.01 3 PLC ± 0.001 4 PLC ± 0.0001 ANGLES $\pm$			
		MATERIAL SEE TABLE siehe Tabelle			
FINISH - -		PRODUCT SPEC 108-94935		SIZE	
		APPLICATION SPEC 114-97587		CAGE CODE 00779	
		WEIGHT SEE TABLE A2		DRAWING NO C-2461722	
		CUSTOMER DRAWING		RESTRICTED TO -	
				SCALE 1:1	
				SHEET 1 of 1	
				REV F	