

VG M32-K67**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG K (standard plastic cable gland), Cable glands, straight, M 32, 15 mm, OD min. 18 - OD max. 25 mm, Polyamide 6
Order No.	1909720000
Type	VG M32-K67
GTIN (EAN)	4032248536641
Qty.	20 pc(s).

VG M32-K67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	41 mm	Height (inches)	1.614 inch
Length	56 mm	Length (inches)	2.205 inch
Net weight	37.5 g		

Temperatures

Operating temperature	-20 °C...80 °C
-----------------------	----------------

General information

AF size 1	42 mm	Cable glands	metric
External thread	M 32	Halogen	No
Length of thread	15 mm	Material	Polyamide 6
Operating temperature range, max.	100 °C	Operating temperature range, min.	-20 °C
Outer cable diameter, max.	25 mm	Outer cable diameter, min.	18 mm
Pitch of thread	1.5 mm	Protection degree	IP67
Seal insert	NBR	Silicone	No
Standards	EN/IEC 62444	Tightening torque	5 Nm
Torque for cap nut, max.	10.5 Nm	Torque for cap nut, min.	9.5 Nm
Torque for connecting adapter, max.	5.5 Nm	Torque for connecting adapter, min.	4.5 Nm
Torque for lock nut, max.	5.5 Nm	Torque for lock nut, min.	4.5 Nm
UL 94 flammability rating	V-2		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32	ECLASS 12.0	27-14-08-01
ECLASS 13.0	27-14-08-01	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/
ROHS	Conform

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity - Standard plastic cable gland made from Polyamide 6 - DE PS2480 220224 001ISS00
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

Creation date June 14, 2025 3:53:43 PM CEST

Catalogue status 07.06.2025 / We reserve the right to make technical changes.