




COIL: @ 25°C

RESISTANCE 100 OHMS $\pm$ 10%

NOMINAL VOLTAGE 5.0 VDC

MUST OPERATE 2.6 VDC

MUST RELEASE 1.4 VDC MAX, 0.23 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX

RELEASE TIME 2.0 MS MAX

CONTACT STABILIZATION TIME 2.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
1A 28 VDC RESISTIVE 100,000
OPERATIONS

DR. R.B. 6/23/97 *[Signature]* 6/23/97

**COMMUNICATIONS
INSTRUMENTS, INC.**

CUST. QPL
CUST. NO. M39016/11-041P

TYPE "JMS" RELAY

JMSC-5XPS