

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

DIN 46247

LOC

A1

DIST

-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F3	REVISED PER ECO-11-005150	21MAR11	RK	HMR

Technical drawing of a FASTON TAB 4.8 connector. The drawing shows a side view of the component with dimensions in mm. Key dimensions include: overall length 13, mounting hole spacing 6.4, pin spacing 3.2 and 3.1, pin diameter 1.35, and a 10-degree taper. A detail view shows a cross-section of the pin with dimensions 5.08 ± 0.1, 3.8, 5.2 ± 0.25, and a 45-degree angle. Surface finish requirements are indicated by triangles 1, 2, and 5.

1

MIN. 4.5 μm Sn OVER MIN. 2.5 μm Cu

2

MIN. 3μm Sn OVER MIN. 0.8μm Ni

3

PACKING: MAX. 3000 PIECES
PACKED INTO CARDBOARD BOX

4

RECOMMENDED DIA. FOR PCB: Ø1.4 -0.1

5

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

1

MIN. 4.5 μm Sn ÜBER MIN. 2.5 μm Cu

2

MIN. 3μm Sn ÜBER MIN. 0.8μm Ni

3

VERPACKUNG: MAX. 3000 TEILE
IN KARTON VERPACKT

4

EMPFOHLENE LEITERPLATTENBOHRUNG: Ø1.4 -0.1

5	OBSOLETE	0.8	1-726389-4	2	CuZn
		0.8	1-726389-3	MIN. 2 μm Ni	CuZn
5	OBSOLETE	0.8	1-726389-2	1	CuZn
		0.5	726389-3	PLAIN BLANK	CuZn
5	OBSOLETE	0.5	726389-2	1	CuZn
		0.5	-726389-1	PLAIN BLANK	CuZn
		"A" DIMENSION MASS	ORDER NO. BESTELL-NR.	SURFACE OBERFLAECHE COLOUR/FARBE	MATERIAL

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0.2

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL
SEE TABLE
SIEHE TABELLE

FINISH
SEE TABLE
SIEHE TABELLE

DWN WEITZEL 28-MAY-85

CHK PFEIFER 28-MAY-85

APVD MORITZ 02-JUL-85

PRODUCT SPEC

ACCORDING TO DIN 46244

APPLICATION SPEC

WEIGHT -

TE Connectivity

NAME

FASTON TAB 4.8
FLACHSTECKER 4.8

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-726389

-

CUSTOMER DRAWING

SCALE 5:1

SHEET 1 OF 1

REV F3

1470-19 (3/11)