



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N2	ECR-26-272619	05MAR2026	ABS	PS



D



SECTION A-A
SCALE 20:1

- 1 .000100 MIN BRIGHT TIN-LEAD OVER .000050 MIN NICKEL ON ENTIRE CONTACT
- 2 .000050 MIN NICKEL ON ENTIRE CONTACT; .000015 MIN GOLD ON CONTACT AREA; .000050 MIN BRIGHT TIN-LEAD ON AREA M.
- 3 .000050 MIN NICKEL ON ENTIRE CONTACT; .000030 MIN GOLD ON CONTACT AREA; .000050 MIN BRIGHT TIN-LEAD ON AREA M.
- 4 LOOSE PIECE CUT-OFF DIMENSION.
- 5 .000015 MIN GOLD ON CONTACT AREA, .000050 MIN TIN ON AREA M, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
- 6 .000030 MIN GOLD ON CONTACT AREA, .000050 MIN TIN ON AREA M, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.


C




SECTION B-B
INSULATION RANGE .025-.060
SCALE 20:1

- 8 .000100 MIN TIN OVER .000050 MIN NICKEL ON ENTIRE CONTACT

B



SECTION C-C
SCALE 20:1



SECTION D-D
SCALE 20:1

LOOSE PIECE STRIP	8 REF	5-104481-6
LOOSE PIECE	6 REF	5-104481-2
LOOSE PIECE STRIP	6 REF	1-104481-3
LOOSE PIECE STRIP	5 REF	1-104481-2
LOOSE PIECE STRIP	6	1-104481-1
LOOSE PIECE STRIP	5	1-104481-0
OBSELETE LOOSE PIECE		104481-9
LOOSE PIECE	3 REF	104481-8
SUPERSEDED BY 1-104481-2 LOOSE PIECE	2 REF	104481-7
SUPERSEDED BY 5-104481-6 LOOSE PIECE	1 REF	104481-6
OBSELETE STRIP		104481-5
STRIP	3	104481-4
STRIP	2	104481-3
STRIP	1	104481-2
REMARKS	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. OBERMAN 5-10-89	TE Connectivity	
		CHK K. HELM 5-12-89		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD R. FLICKER 5-12-89	NAME	CONTACT, CRIMP SNAP-IN AMPMODU SHORT POINT, 28-32 AWG
	0. PLC ± -	PRODUCT SPEC	SIZE	RESTRICTED TO
	1. PLC ± -	108-1472	CAGE CODE	A100779
	2. PLC ± -	APPLICATION SPEC	DRAWING NO	
MATERIAL PHOSPHOR BRONZE	3. PLC ± .005	114-25038	104481	REV N2
	4. PLC ± -	WEIGHT	104481	
SEE TABLE		CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 1