




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
J		ECN-23-227208; DRW REG W/CREO	08AUG2023	DR	JHW
K	REV PER	ECN-24-278317	02AUG2024	JAB	JW



- NOTES:
- MATES WITH TEC P/N 212013-1 IN AMPLIMITE CONNECTOR ASSEMBLIES ONLY
 - APPROVED CRIMP TOOLING: DANIELS CRIMP TOOL P/N FT8, DANIELS POSITIONER P/N TP731, STRIP LENGTH = .375 [9.53], #16 AWG SETTING 8, #18 AWG SETTING 6.
NOTE: USE OF ANY UNAPPROVED TOOLING WILL RESULT IN CRIMPED TERMINATIONS THAT ARE NOT QUALIFIED
 - WIRE BARREL ACCEPTS #16 -#18 AWG STRANDED WIRE
- RETENTION CLIP DIAMETER TO BE MEASURED WITH RING GAGE
5. FINISH:
CONTACT: GOLD PLATE .000050 [.00127] MIN THK PER ASTM-B-488 OVER
NICKEL UNDERPLATE .000050 [.00127] MIN THK PER PER QQ-N-290
RETENTION CLIP: NICKEL PLATE .000050 [.00127] MIN THK PER PER QQ-N-290

RESTRICTED PART NUMBER

	1-212014-1
	212014-2
	212014-1
	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS 10NOV2000	TE Connectivity	
		CHK D. MILLER 10NOV2000		
DIMENSIONS: IN [MM]		APVD D. MILLER 10NOV2000	NAME CONTACT ASSY, SOCKET CRIMP TYPE, SIZE 8, WIRE SIZE 16-18 AWG	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.005 (0.13) 4 PLC ± ANGLES ± FINISH ±	APPLICATION SPEC	
		WEIGHT -		RESTRICTED TO -
MATERIAL -		SIZE A		CAGE CODE 00779
		DRAWING NO 212014		REV K
CUSTOMER DRAWING		SCALE 10:1		SHEET 1 OF 1