

© -TE Connectivity. All Rights Reserved.

CONNETTORE TIPO B (CON MOLLA DI RITEGNO INTERNA)
CONNECTOR TYPE B (WITH INTERNAL SPRING)

17.0 ±0.5

12.8 ±0.5

1.5 COST.

37.5 ±0.5

5.0 ±0.5

0.8 COST.

AMP

1

2

3

SEZIONE A-A
(SECTION A-A)

11.8 ±0.5

25° COST.

3.0 ±0.5

1.0

2.2

1.3

1.0

1.5

16.0 ±0.5

12.3 ±0.3

Ø0.9 ±0.05
SPRING WIRE
DIAMETER

TOP

VISTA DA K
(VIEW FROM K)

3.3 +0.3
-0.1

+0.2

1.6 -0.1

9.9 ±0.6

17.3 ±0.3
AT TOP

TIP. CAVITA' PER TERMINALI AMP JPT P/N 929939-...
OPPURE 929937-... E RELATIVI GOMMINI
AMP P/N 828904-1, 828905-1, 282536-1.
TAPPO CAVITA' P/N 828906-2
(TYP. CAV. FOR JPT CONT. P/N 929939-.. A/O 929937-.. AND REL.
SINGLE WIRE SEAL P/N 828904-1, 828905-1, 282536-1
CAVITY PLUG P/N 828906-2)

PASSO 5.0 ±0.15
(PITCH 5.0 ±0.15)

17.5 ±0.5

R 5.5 ±1.0

R 16.8 ±1.0

23.0 ±0.5

ASSE CAVITA'
(CAVITY CENTER LINE)



ASSE CONNETTORE
(CONNECTOR CENTER LINE)

OBSOLETE	ROSSO (RED)	282190-8
OBSOLETE	GIALLO (YELLOW)	282190-7
	MARRONE (BROWN)	282190-6
OBSOLETE	BLU (BLUE)	282190-5
OBSOLETE	VERDE (GREEN)	282190-4
OBSOLETE	NATURALE (NATURAL)	282190-3
	GRIGIO (GREY)	282190-2
	NERO (BLACK)	282190-1
	COLORE COLOR	NUMERO PART. No


3	////	ACCIAIO INOX (STAINLESS STEEL)	MOLLA (SPRING)
2	NATURALE (NATURAL)	GOMMA SILICONICA (SILICONE RUBBER)	GUARNIZIONE (RUBBER GASKET)
1	////	PA 6.6 C.VETRO (PA 6.6-GF)	BLOCCETTO (HOUSING)
		MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Ennio CINI 9 NOV 90	TE Connectivity Ltd.	
DIMENSIONS: mm		CHK C.TARTARI 13 OCT 92	2 W.SPLASH PROOF CONN.ASS'Y with SECONDARY LOCK	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME	
0 PLC ± -		PRODUCT SPEC	SIZE	
1 PLC ± 0.3		APPLICATION SPEC	CAGE CODE	
2 PLC ± -			DRAWING NO	
3 PLC ± -			RESTRICTED TO	
4 PLC ± -				
ANGLES ± 2°		WEIGHT	A2 00779 C=282190	
MATERIAL		FINISH	CUSTOMER DRAWING	
DIAM. ISOLANTE (INS. DIA. RANGE) 1.5-3.0mm (REDUCED INS.CABLE)		RANGO FILO (WIRE RANGE) 0.5-2.5 mm²	SCALE NTS	
METRIC			SHEET 1 OF 2	
			REV M3	

1471-9 (1/15)




DETT. CONTATTO SC. 5:1
(TAB DETAIL SC. 5:1)



FORMA ALTERNATIVA PERMESSA CON RAGGIO
(ALLOWED ALTERNATIVE PROFILE WITH RADIUS)

- 1 QUOTE APPLICABILI PER SFORMATURA PEZZO (RIGHT DIMENSIONS FOR EXTRACTION ITEM FROM THE MOULD)
- 2 MATERIALE CONTATTI: LEGA DI RAME STAGNATA, ES. OTTONE STAGNATO. (TAB MATERIAL: TINNED Cu ALLOY, E.G. TINNED BRASS)
- 3 MATERIALE BLOCCHETTO: TERMOPLASTICO CARICATO FIBRA VETRO. (HOUSING MATERIAL: THERMOPLASTIC GLASS FIBER FILLED).



DIAM. ISOLANTE (INS. DIA. RANGE) SEE SHEET 1		RANGO FILO (WIRE RANGE) SEE SHEET 1		FINITURA / COLORE (FINISH / COLOUR)		MATERIALE (MATERIAL)		NUMERO (PART NUMBER)	
THIS DRAWING IS A CONTROLLED DOCUMENT.				CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN -		CHK -		APVD -	
		0 PLC ± -		PRODUCT SPEC		NAME		2 POS.SPLASH PROOF CONN.ASS'Y with SECONDARY LOCK	
		1 PLC ± 0.3		APPLICATION SPEC		SIZE		CAGE CODE	
		2 PLC ± -		WEIGHT		DRAWING NO		RESTRICTED TO	
		3 PLC ± -		CUSTOMER DRAWING		SCALE		SHEET	
MATERIAL		FINISH		4 PLC ± -		A2 00779		C=282190	
				ANGLES ± 2°		M3			