


REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APVD
	G4	ECR-25-236041	25AUG2025	SY	DR




AMP WIRE RANGE	 E13288 Listed
2/0 AWG SOLID OR STRANDED	2/0 AWG STRANDED

 LR7189 Certified
2/0 AWG SOLID OR STRANDED

- 1 STAMP AMP 2/OW* APPROX AS SHOWN
- 2 TIN PL 0.00254[.000100] MIN EXT THK PER ASTM B-545
- 3 BRIGHT TIN LEAD PL 0.00254[.000100] MIN THK PER ASTM B-545
- 4 NICKEL PLATE 0.00762 [.000300] MIN EXT. THK PER SAE AMS QQ-N-290
- 5 NOTE DELETED

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: SEE TABLE
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 60.6-76.3mm ² [119,500-150,500] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

OBSOLETE	170°C[338°F]	50	LOOSE PIECE	 3	2-321871-2
	343°C[650°F]	50	LOOSE PIECE	 4	321871-2
	170°C[338°F]	50	LOOSE PIECE	 2	321871
	MAX OPERATIVE TEMPERATURE	QTY	PACKAGE TYPE	FINISH	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN DK SCHRUM 1/14/94 CHK AJ KAUFMAN 1/19/94 APVD JL MECKLEY 1/19/94	 TE Connectivity	
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME TERMINAL, RING TONGUE, SOLISTRAND	
		FINISH SEE TABLE		SIZE A2	CAGE CODE 00779
MATERIAL COPPER PER ASTM B-152 ANNEALED		WEIGHT -		DRAWING NO C=321871	
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1	REV G4