


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H4	REVISED PER ECR-25-255998	11SEP2025	SA	DSC


- 1 WIRE INSULATION DIA, SEE TABLE "A"
- 2 TONGUE MATL THK, 0.789±0.05 [.031±.002].
- 3

BODY: PHOS BRONZE PER ASTM B103
INSULATION: NYLON
SLEEVE: COPPER PER ASTM B152
- 4

BODY: TIN PLATE PER ASTM B545
SLEEVE: TIN PLATE PER ASTM B545
INSULATION: COLOR-BLUE



.115-.170	1 KIT = 250 PIECES	LOOSE PIECE	6-52421-0
.115-.170	5000	ON TAPE, REEL	52421-3
.115-.170	--	LOOSE PIECE	52421-1
.105-.150	--	LOOSE PIECE	52421
DIM "A"	QTY	PACKAGE TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr_ruth 14MAY10	 TE Connectivity		
		CHK TOM MICHIELUTTI 14MAY10			
DIMENSIONS: MM [INCHES]		APVD TOM MICHIELUTTI 14MAY10	NAME TERMINAL, PIDG, SPRING SPADE, WIRE SIZE: 16-14 AWG		
		PRODUCT SPEC —			
		APPLICATION SPEC —			
MATERIAL 3		WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-52421
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.2 [.008] 3 PLC ± — 4 PLC ± — ANGLES ± 5° FINISH 4		RESTRICTED TO —			
CUSTOMER DRAWING			SCALE 6:1	SHEET 1 OF 1	REV H4