


P	LTR	DESCRIPTION	DATE	DWN	APVD
	S	HOUSING RESIN CHANGED	270CT2021	SCB	KJK
	T	RIB FEATURE IS ADDED IN THE STANDOFF FEATURE	19FEB2026	RS	GVP



SUPERSEDED BY 7-534206-1

6-5	$\frac{2}{2}$	99.06[3.900]	101.60[4.000]	80	4-534206-0
	$\frac{2}{2}$	96.52[3.800]	99.06[3.900]	78	3-534206-9
	$\frac{2}{2}$	93.98[3.700]	96.52[3.800]	76	3-534206-8
	$\frac{2}{2}$	91.44[3.600]	93.98[3.700]	74	3-534206-7
	$\frac{2}{2}$	88.90[3.500]	91.44[3.600]	72	3-534206-6
	$\frac{2}{2}$	86.36[3.400]	88.90[3.500]	70	3-534206-5
	$\frac{2}{2}$	83.82[3.300]	86.36[3.400]	68	3-534206-4
	$\frac{2}{2}$	81.28[3.200]	83.82[3.300]	66	3-534206-3
	$\frac{2}{2}$	78.74[3.100]	81.28[3.200]	64	3-534206-2
	$\frac{2}{2}$	76.20[3.000]	78.74[3.100]	62	3-534206-1
	$\frac{2}{2}$	73.66[2.900]	76.20[3.000]	60	3-534206-0
	$\frac{2}{2}$	71.12[2.800]	73.66[2.900]	58	2-534206-9
	$\frac{2}{2}$	68.58[2.700]	71.12[2.800]	56	2-534206-8
	$\frac{2}{2}$	66.04[2.600]	68.58[2.700]	54	2-534206-7
	$\frac{2}{2}$	63.50[2.500]	66.04[2.600]	52	2-534206-6
	$\frac{2}{2}$	60.96[2.400]	63.50[2.500]	50	2-534206-5
	$\frac{2}{2}$	58.42[2.300]	60.96[2.400]	48	2-534206-4
	$\frac{2}{2}$	55.88[2.200]	58.42[2.300]	46	2-534206-3
	$\frac{2}{2}$	53.34[2.100]	55.88[2.200]	44	2-534206-2
	6-1	$\frac{2}{2}$	50.80[2.000]	53.34[2.100]	42
$\frac{2}{2}$		48.26[1.900]	50.80[2.000]	40	2-534206-0
$\frac{2}{2}$		45.72[1.800]	48.26[1.900]	38	1-534206-9
$\frac{2}{2}$		43.18[1.700]	45.72[1.800]	36	1-534206-8
$\frac{2}{2}$		40.64[1.600]	43.18[1.700]	34	1-534206-7
$\frac{2}{2}$		38.10[1.500]	40.64[1.600]	32	1-534206-6
$\frac{2}{2}$		35.56[1.400]	38.10[1.500]	30	1-534206-5
$\frac{2}{2}$		33.02[1.300]	35.56[1.400]	28	1-534206-4
$\frac{2}{2}$		30.48[1.200]	33.02[1.300]	26	1-534206-3
$\frac{2}{2}$		27.94[1.100]	30.48[1.200]	24	1-534206-2
	$\frac{2}{2}$	25.40[1.000]	27.94[1.100]	22	1-534206-1
	$\frac{2}{2}$	22.86[.900]	25.40[1.000]	20	1-534206-0
	$\frac{2}{2}$	20.32[.800]	22.86[.900]	18	534206-9
	$\frac{2}{2}$	17.78[.700]	20.32[.800]	16	534206-8
	$\frac{2}{2}$	15.24[.600]	17.78[.700]	14	534206-7
	$\frac{2}{2}$	12.70[.500]	15.24[.600]	12	534206-6
	$\frac{2}{2}$	10.16[.400]	12.70[.500]	10	534206-5
	$\frac{2}{2}$	7.62[.300]	10.16[.400]	8	534206-4
	$\frac{2}{2}$	5.08[.200]	7.62[.300]	6	534206-3
	$\frac{2}{2}$	2.54[.100]	5.08[.200]	4	534206-2
$\frac{2}{2}$	-	2.54[.100]	2	$\frac{6}{6}$ 534206-1	
	FINISH	B	A	NO OF POSN	PART NUMBER

- 1 HOUSING: FLAME RETARDANT, GLASS FILLED, THERMOPLASTIC, COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE
- 2 CONTACT: DUPLEX PLATED 0.00076[.000030] MIN GOLD IN CONTACT AREA,
0.00381-0.00762[.000150 -.000300] BRIGHT TIN-LEAD ON LEADS
ALL OVER 0.00127[.000050] MINIMUM NICKEL.
- 3 THESE DIMENSIONS PERTAIN TO CAVITIY CENTERLINES ONLY - NOT TO CONTACT LOCATIONS
- 4 PART NUMBER AND DATE CODE ARE MARKED IN APPROXIMATE LOCATION SHOWN,EITHER SIDE.
- 5 TOLERANCE IS NON-CUMULATIVE.
- 6 2 POSITION DATE CODE IS MARKED OPPOSITE SIDE OF TE CONNECTIVITY LOGO.
- 7 POINT-OF-MEASUREMENT DIMENSION FOR PLATING THICKNESS (INSIDE CONTACT BEAM).
- 8 POINT-OF-CONTACT DIMENSION.
- 9 NO PART NUMBER MARKING REQUIRED FOR THIS PART.
- 10 TE LOGO AND CSA LOGO ARE MOLDED INTO HOUSING.
- 11 CONTACT: DUPLEX PLATED 0.00076[.000030] MIN GOLD IN CONTACT AREA,
0.00381-0.00762[.000150 -.000300] MATTE TIN ON LEADS,
ALL OVER 0.00127[.000050] MIN NICKEL
- 12 ROHS 2002/95/EC COMPLIANT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. BINNER 06NOV02 CHK J. OLSON 06NOV02 APVD J. OLSON 06NOV02		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±: 1 PLC ±: 2 PLC ±-.10 [.005] 3 PLC ±: 4 PLC ±: ANGLES ±: FINISH		NAME RCPT. ASSY., MOD II, DBL ROW, .100 X .100 DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU	
		PRODUCT SPEC 108-25022 APPLICATION SPEC 114-25018		SIZE A2	
MATERIAL  SEE TABLE		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C=534206	
				RESTRICTED TO -	
				SCALE 5:1	
				SHEET 1 OF 2	
				REV T	

4

3

2

I

© 2025 TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

11	99.06[3.900]	101.60[4.000]	80	12	9-534206-0
11	96.52[3.800]	99.06[3.900]	78	12	8-534206-9
11	93.98[3.700]	96.52[3.800]	76	12	8-534206-8
11	91.44[3.600]	93.98[3.700]	74	12	8-534206-7
11	88.90[3.500]	91.44[3.600]	72	12	8-534206-6
11	86.36[3.400]	88.90[3.500]	70	12	8-534206-5
11	83.82[3.300]	86.36[3.400]	68	12	8-534206-4
11	81.28[3.200]	83.82[3.300]	66	12	8-534206-3
11	78.74[3.100]	81.28[3.200]	64	12	8-534206-2
11	76.20[3.000]	78.74[3.100]	62	12	8-534206-1
11	73.66[2.900]	76.20[3.000]	60	12	8-534206-0
11	71.12[2.800]	73.66[2.900]	58	12	7-534206-9
11	68.58[2.700]	71.12[2.800]	56	12	7-534206-8
11	66.04[2.600]	68.58[2.700]	54	12	7-534206-7
11	63.50[2.500]	66.04[2.600]	52	12	7-534206-6
11	60.96[2.400]	63.50[2.500]	50	12	7-534206-5
11	58.42[2.300]	60.96[2.400]	48	12	7-534206-4
11	55.88[2.200]	58.42[2.300]	46	12	7-534206-3
11	53.34[2.100]	55.88[2.200]	44	12	7-534206-2
11	50.80[2.000]	53.34[2.100]	42	12	7-534206-1
11	48.26[1.900]	50.80[2.000]	40	12	7-534206-0
11	45.72[1.800]	48.26[1.900]	38	12	6-534206-9
11	43.18[1.700]	45.72[1.800]	36	12	6-534206-8
11	40.64[1.600]	43.18[1.700]	34	12	6-534206-7
11	38.10[1.500]	40.64[1.600]	32	12	6-534206-6
11	35.56[1.400]	38.10[1.500]	30	12	6-534206-5
11	33.02[1.300]	35.56[1.400]	28	12	6-534206-4
11	30.48[1.200]	33.02[1.300]	26	12	6-534206-3
11	27.94[1.100]	30.48[1.200]	24	12	6-534206-2
11	25.40[1.000]	27.94[1.100]	22	12	6-534206-1
11	22.86[.900]	25.40[1.000]	20	12	6-534206-0
11	20.32[.800]	22.86[.900]	18	12	5-534206-9
11	17.78[.700]	20.32[.800]	16	12	5-534206-8
11	15.24[.600]	17.78[.700]	14	12	5-534206-7
11	12.70[.500]	15.24[.600]	12	12	5-534206-6
9	11	10.16[.400]	10	12	5-534206-5
9	11	7.62[.300]	8	12	5-534206-4
9	11	5.08[.200]	6	12	5-534206-3
9	11	2.54[.100]	4	12	5-534206-2
6	9	11	2	12	5-534206-1
FINISH		B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±0.13[.005]
3 PLC ±-
4 PLC ±-
ANGLES ±-
FINISH

SEE TABLE

DWN
M.BINNER
CHK
J.OLSON
APVD
J.OLSON
PRODUCT SPEC
108-25022
APPLICATION SPEC
114-25018
WEIGHT
-

06NOV02
06NOV02
06NOV02

CUSTOMER DRAWING

TE Connectivity

RCPT. ASSY., MOD II, DBL ROW, .100 X .100
DOUBLE ROW, DUAL ENTRY, .100X.100CL,
VERTICAL MOUNT, AMPMODU

SIZE
A2

CAGE CODE
00779

DRAWING NO
534206

RESTRICTED TO
-

SCALE
5:1

SHEET
2

OF
2

REV
T

1471-9 (3/13)