



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED PER ECR-24-207629	16MAY2024	SA	DSC

- 1

STAMP "AMP 16-14 HD*" LOCATED APPROX AS SHOWN.
- 2 TONGUE MATERIAL THK IS .050 MAX
- 3 FOR .230 MAX WIRE INSULATION DIA.



BODY & SLEEVE: COPPER PER ASTM B152 TIN LEAD (93-7) PLATE PER ASTM B545 (3% MIN LEAD CONTENT) INSULATION: PVF2, COLOR - NATURAL	53982-1
MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 14SEP04	TE Connectivity					
		CHK T MICHIELUTTI 14SEP04						
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T MICHIELUTTI 14SEP04	NAME WIRE TERMINAL PVF2 – PIDG – RING TONGUE WIRE SIZE : 16–14 HD					
		PRODUCT SPEC —						
	0 PLC ± – 1 PLC ± – 2 PLC ± – 3 PLC ± .008 4 PLC ± – ANGLES ± 5°	APPLICATION SPEC —	SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
		WEIGHT —	A3		00779	C-53982	—	
MATERIAL —	FINISH —	CUSTOMER DRAWING				SCALE 5:1	SHEET 1 OF 1	REV F