

SPECIFICATION CONTROL DRAWING

55A3112

TITLE ONE CONDUCTOR CABLE, SHIELDED, GENERAL PURPOSE, 600 VOLT

Date 11-14-11

Revision A

This specification sheet forms a part of the latest issue of Raychem Specification 55A.

COMPONENT WIRE - 55A0112

SHIELD - SILVER-COATED COPPER



CABLE CONSTRUCTION DETAILS					
PART NUMBER <u>1/</u>	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	OUTSIDE DIAMETER (inches)		MAXIMUM WEIGHT (lbs/1000 ft.)
			NOMINAL	MAXIMUM	
55A3112-30-*	30	38	.041	.044	2.3
55A3112-28-*	28	38	.044	.047	2.7
55A3112-26-*	26	38	.049	.052	3.4
55A3112-24-*	24	38	.054	.057	4.3
55A3112-22-*	22	38	.060	.063	5.4
55A3112-20-*	20	38	.067	.070	7.2
55A3112-18-*	18	38	.077	.080	10.0
55A3112-16-*	16	38	.085	.088	12.2
55A3112-14-*	14	38	.102	.106	17.7
55A3112-12-*	12	38	.120	.124	25.3

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

SHIELD COVERAGE: 85% (minimum)

PART NUMBER:

The "*" in the part numbers above shall be replaced by a color code designator.

1/ Example: AWG 20, white component wire: 55A3112-20-9

NOTE: Nominal values are for information only.

Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.