


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	ECR-26-274353	23MAR2026	ABS	PS



- 1
- WIRE RANGE: #20-#24.
- 2
- INSULATION RANGE: .069 MAX. DIA.
- 3
- FOR SECTIONS AND ADDITIONAL DIMENSIONS SEE AMP CUSTOMER DRAWING#85969.

OBSOLETE	86016-6	GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT,.000050 GOLD IN CONTACT AREA
	86016-5	GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT,.000015 GOLD IN CONTACT AREA
OBSOLETE	86016-4	.000050 GOLD OVER .000050 NICKEL
	86016-3	PREPLATED:(HALT).000078-.000158 BRIGHT TIN
	86016-2	GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT,.000030 GOLD IN CONTACT AREA
	86016-1	.000030 GOLD OVER .000050 NICKEL
	PART NUMBER	FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.C. CLAYBAUGH	TE Connectivity					
		CHK						
		APVD						
		PRODUCT SPEC						
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE CONTACT, MOD IV CRIMP SNAP-IN LOOSE PIECE					
	0 PLC ± -		SIZE					
	1 PLC ± -		CAGE CODE					
	2 PLC ± -		DRAWING NO					
	3 PLC ± -		RESTRICTED TO					
	4 PLC ± -		A300779					
	ANGLES ± -		C-86016					
MATERIAL CU-NI-SI	FINISH -	WEIGHT -	CUSTOMER DRAWING					
			SCALE 10:1	SHEET 1 OF 1	REV C2			