



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	TABLE DIMENSIONS UPDATED	15APR2026	GSK	AK



Product Size	2.4	3.2	4.8	6.4	9.5	12.7	19.0	25.4	38.1
"D" Minimum Supplied I.D.	2.40 (.094)	3.20 (.126)	4.80 (.189)	6.40 (.250)	9.50 (.375)	12.70 (.500)	19.05 (.750)	25.40 (1.00)	38.10 (1.50)
"d" Maximum Recovered I.D.	1.19 (.047)	1.60 (.063)	2.40 (.094)	3.20 (.126)	4.80 (.189)	6.40 (.250)	9.50 (.375)	12.70 (.500)	19.05 (.750)
"w" Recovered Wall Thickness	0.50±0.10 (.020±.004)	0.50±0.10 (.020±.004)	0.51±0.11 (.020±.004)	0.65±0.15 (.026±.006)	0.65±0.15 (.026±.006)	0.65±0.15 (.026±.006)	0.75±0.15 (.030±.006)	0.90±0.15 (.035±.006)	1.00±0.20 (.039±.008)
Minimum Sleeve Flattened Width	4.90 (.193)	6.50 (.256)	8.90 (.350)	11.00 (.433)	15.70 (.618)	20.70 (.815)	30.70 (1.209)	41.10 (1.618)	61.00 (2.402)

- NOTES:
1. ALL DIMENSIONS ARE IN MILLIMETERS (inches).
 2. ONE SPLICE PER SPOOL PERMITTED.
BOX IS MARKED WHERE APPLICABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AFK CHK —	15JAN2020	 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		APVD LS		HX-CT			
		PRODUCT SPEC		OUTSIDE PRINTER SPOOL			
		RW-2072		—			
		APPLICATION SPEC		—			
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
CROSSLINKED POLYOLEFIN		—		411-121008	A30198G	C-MCD170013	—
CUSTOMER DRAWING				SCALE		SHEET	REV
				NTS		1 OF 1	A2