

IE-USB-3.0-A-A-3M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Version	USB cable, USB A 3.0, USB A 3.0, PVC, 3 m
Order No.	2581730030
Type	IE-USB-3.0-A-A-3M
GTIN (EAN)	4050118630534
Qty.	1 pc(s).

IE-USB-3.0-A-A-3M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Length	3 m	Length (inches)	118.11 inch
Net weight	140 g		

Temperatures

Operating temperature	-15 °C...80 °C
-----------------------	----------------

Technical specifications for cable

Sheathing colour	blue
------------------	------

General technical data

Contact surface	Gold over nickel
-----------------	------------------

Cable structure

Cross-section	4*AWG30 + 2*AWG30 + 2*AWG20 (Power)	Material sheath	PVC
Sheath diameter, max.	5.65 mm	Sheath diameter, min.	5.35 mm
Sheathing colour	blue		

Plug, left

Plug left	USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded
-----------	--

Plug, right

Plug right	USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded
------------	--

Classifications

ETIM 6.0	EC001408	ETIM 7.0	EC001408
ETIM 8.0	EC001408	ETIM 9.0	EC001408
ETIM 10.0	EC001408	ECLASS 9.0	27-06-20-11
ECLASS 9.1	27-06-90-90	ECLASS 10.0	27-06-01-06
ECLASS 11.0	27-06-01-06	ECLASS 12.0	27-06-01-06
ECLASS 13.0	27-06-01-06	ECLASS 14.0	27-06-01-06
ECLASS 15.0	27-06-01-06		

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/
ROHS	Conform

IE-USB-3.0-A-A-3M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Product Change Notification	Technical change sheathing colour of USB cable 3.0 Technische Änderung Mantelfarbe des USB-Kabel 3.0
Catalogues	Catalogues in PDF-format