




COIL: @ 25°C

RESISTANCE 1025 OHMS $\pm 10\%$

NOMINAL VOLTAGE 12.0 VDC

MUST OPERATE 7.0 VDC

MUST RELEASE 4.0 VDC MAX, 0.63 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4 MS MAX

RELEASE TIME 2.5 MS MAX

CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 1/11/96

CK. *V. V. V. V. V.*



COMMUNICATIONS
INSTRUMENTS, INC.

CUST. QPL

CUST. NO. M39016/10-035L

TYPE "J1MS" RELAY

J1MSC-12XL