

## REVISIONS

| P | LTR | DESCRIPTION               | DATE       | DWN | APVD |
|---|-----|---------------------------|------------|-----|------|
|   | P2  | REVISED PER ECR-26-279619 | 29/05/2026 | AJ  | ME   |





TABLE OF DIMENSIONS


| PART NUMBER | H              |                | J              |                |               | P               | JO              | R             | S            | T              | U              | HW            | JW             |
|-------------|----------------|----------------|----------------|----------------|---------------|-----------------|-----------------|---------------|--------------|----------------|----------------|---------------|----------------|
|             | Min            | Max            | Min            | Min            | Max           | ±10%            | ±10%            | Ref           | Ref          | Ref            | ±10%           | ±20%          | ±20%           |
|             | a              | b              | -3,-4,-25<br>a | -12,-100<br>a  | b             | b               | b               | b             | b            | b              | b              | b             | b              |
| 202D211     | 22.4<br>[.88]  | 11.4<br>[.45]  | 22.4<br>[.88]  | 14.0<br>[.55]  | 6.4<br>[.25]  | 105.9<br>[4.17] | 86.4<br>[3.40]  | 11.7<br>[.46] | 3.0<br>[.12] | 1.0<br>[.04]   | 14.2<br>[.56]  | 1.52<br>[.06] | 1.14<br>[.045] |
| 202D221     | 25.7<br>[1.01] | 15.0<br>[.59]  | 25.7<br>[1.01] | 16.0<br>[.63]  | 7.4<br>[.29]  | 121.2<br>[4.77] | 98.6<br>[3.88]  | 12.2<br>[.48] | 3.0<br>[.12] | 1.0<br>[.04]   | 15.0<br>[.59]  | 1.52<br>[.06] | 1.14<br>[.045] |
| 202D232     | 29.5<br>[1.16] | 18.8<br>[.74]  | 29.5<br>[1.16] | 18.3<br>[.72]  | 8.4<br>[.33]  | 138.7<br>[5.46] | 112.8<br>[4.44] | 12.2<br>[.48] | 3.0<br>[.12] | 1.0<br>[.04]   | 15.5<br>[.61]  | 1.78<br>[.07] | 1.14<br>[.045] |
| 202D242     | 34.0<br>[1.34] | 22.9<br>[.90]  | 34.0<br>[1.34] | 21.3<br>[.84]  | 9.7<br>[.38]  | 159.5<br>[6.28] | 130.8<br>[5.15] | 12.2<br>[.48] | 3.0<br>[.12] | 1.0<br>[.04]   | 15.7<br>[.62]  | 1.78<br>[.07] | 1.14<br>[.045] |
| 202D253     | 37.3<br>[1.47] | 29.5<br>[1.16] | 37.3<br>[1.47] | 23.1<br>[.91]  | 10.4<br>[.41] | 177.8<br>[7.00] | 142.2<br>[5.60] | 14.0<br>[.55] | 3.0<br>[.12] | 1.65<br>[.065] | 18.0<br>[.71]  | 2.0<br>[.08]  | 1.14<br>[.045] |
| 202D263     | 43.7<br>[1.72] | 34.0<br>[1.34] | 43.7<br>[1.72] | 27.2<br>[1.07] | 12.2<br>[.48] | 203.2<br>[8.00] | 163.1<br>[6.42] | 15.2<br>[.60] | 3.0<br>[.12] | 1.65<br>[.065] | 19.8<br>[.78]  | 2.0<br>[.08]  | 1.14<br>[.045] |
| 202D274     | 50.0<br>[1.97] | 41.2<br>[1.62] | 50.0<br>[1.97] | 31.5<br>[1.24] | 14.2<br>[.56] | 203.2<br>[8.00] | 157.7<br>[6.21] | 15.2<br>[.60] | 3.0<br>[.12] | 1.65<br>[.065] | 20.8<br>[.82]  | 2.3<br>[.09]  | 1.40<br>[.055] |
| 202D285     | 62.7<br>[2.47] | 47.0<br>[1.85] | 62.7<br>[2.47] | 39.1<br>[1.54] | 17.5<br>[.69] | 203.2<br>[8.00] | 153.2<br>[6.03] | 16.0<br>[.63] | 3.0<br>[.12] | 2.0<br>[.08]   | 23.4<br>[.92]  | 2.5<br>[.10]  | 1.40<br>[.055] |
| 202D296     | 69.3<br>[2.73] | 59.7<br>[2.35] | 69.3<br>[2.73] | 43.2<br>[1.70] | 19.6<br>[.77] | 203.2<br>[8.00] | 143.3<br>[5.64] | 16.0<br>[.63] | 3.0<br>[.12] | 2.0<br>[.08]   | 23.6<br>[.93]  | 2.5<br>[.10]  | 1.40<br>[.055] |
| 202D299     | 81.8<br>[3.22] | 67.1<br>[2.64] | 81.8<br>[3.22] | 51.1<br>[2.01] | 22.9<br>[.90] | 203.2<br>[8.00] | 138.4<br>[5.45] | 16.0<br>[.63] | 3.0<br>[.12] | 2.0<br>[.08]   | 31.2<br>[1.23] | 2.5<br>[.10]  | 1.40<br>[.055] |

DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

|        |              |
|--------|--------------|
| 0 PLC  | ± -          |
| 1 PLC  | ± 0.50[.1]   |
| 2 PLC  | ± 0.25[.01]  |
| 3 PLC  | ± 0.13[.005] |
| 4 PLC  | ± -          |
| ANGLES | ± 1°         |



DWN 03/15/2021

M MAZARIEGOS

CHK 03/16/2021

M TAYLOR

APVD 03/16/2021

L RODRIGUEZ

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

MATERIAL

SEE SHEET 2

FINISH

-



TE Connectivity Ltd.

NAME

BOOT, STRAIGHT,  
WITH LIP

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

00779

C- 202D211-XX-0THRU299-XX-0

-

CUSTOMER DRAWING

SCALE

DNS

SHEET

1 OF 2

REV P2

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

TE Connectivity Ltd.

COPYRIGHT

©

THIS DRAWING IS UNPUBLISHED.

## REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
|   | —   | SEE SHEET 1 | —    | —   | —    |

## COMPATIBILITY CHART

| MATERIAL DASH NO. | MATERIAL DESCRIPTION              | RT SPEC | COATING SLASH NUMBER | COATING S NUMBER  |
|-------------------|-----------------------------------|---------|----------------------|-------------------|
| -3                | Polyolefin, Semi-rigid            | RT-301  | /42;/86;/180         | S1017;S1048;S1030 |
| -4                | Polyolefin, Flexible              | RT-1304 | /42;/86;/180         | S1017;S1048;S1030 |
| -12               | Fluoroelastomer,Flexible          | RT-1312 | N/A                  | N/A               |
| -25               | Elastomer, Fluid Resistant        | RW-2070 | /42;/86;/225         | S1017;S1048;S1206 |
| -100              | Polyolefin, Semi-flexible ZEROHAL | RW-2082 | /86,/180             | S1048,S1030       |

## ORDERING INFORMATION

BASE PART NUMBER 202D211 -XX -XX /XX -0  
 MATERIAL DASH NUMBER                       
 (SEE COMPATABILITY CHART)  
 MODIFICATION NUMBER                       
 ADHESIVE SLASH NUMBER                       
 (IF NECESSARY, SEE COMPATABILITY CHART)  
 COLOR DESIGNATOR                     

## NOTES:

- DIMENSIONS APPEARING IN TABLE ARE AS FOLLOWS:  
 a - AS SUPPLIED  
 b - AFTER UNRESTRICTED RECOVERY
- COATING IS OPTIONAL. AS SUPPLIED DIMENSIONS APPEARING IN TABLE ARE FOR UNCOATED PARTS. WHEN COATING IS ADDED, ENTRY DIAMETERS WILL BE REDUCED BY 1.5mm[.06] MAX.
- MOLDING PORTS ARE OPTIONAL. WHEN -00 MODIFICATION NUMBER IS SPECIFIED MOLDING PORTS WILL BE LOCATED AS SHOWN.


RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

COPYRIGHT - TE Connectivity Ltd.



THIS DRAWING IS UNPUBLISHED.

|                                                                                                                                                    |  |                                   |                                                                                                           |                                          |                    |  |
|----------------------------------------------------------------------------------------------------------------------------------------------------|--|-----------------------------------|-----------------------------------------------------------------------------------------------------------|------------------------------------------|--------------------|--|
| DIMENSIONS:<br>mm [INCHES]                                                                                                                         |  | DWN<br>M MAZARIEGOS<br>03/15/2021 | MATERIAL<br>—                                                                                             |                                          | FINISH<br>—        |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:<br><br>0 PLC ± —<br>1 PLC ± 0.50[.1]<br>2 PLC ± 0.25[.01]<br>3 PLC ± 0.13[.005]<br>4 PLC ± —<br>ANGLES ± 1° |  | CHK<br>M TAYLOR<br>03/16/2021     |  TE Connectivity Ltd. |                                          |                    |  |
|                                                                                                                                                    |  | APVD<br>L RODRIGUEZ<br>03/16/2021 |                                                                                                           |                                          |                    |  |
|                                                                                                                                                    |  | PRODUCT SPEC<br>—                 | NAME<br>BOOT, STRAIGHT,<br>WITH LIP                                                                       |                                          |                    |  |
|                                                                                                                                                    |  | APPLICATION SPEC<br>—             |                                                                                                           |                                          |                    |  |
|                                                                 |  | SIZE<br>A4                        | CAGE CODE<br>00779                                                                                        | DRAWING NO<br>C-202D211-XX-0THRU299-XX-0 | RESTRICTED TO<br>— |  |
|                                                                                                                                                    |  | WEIGHT                            |                                                                                                           |                                          | CUSTOMER DRAWING   |  |
| SCALE<br>DNS                                                                                                                                       |  | SHEET<br>2 OF 2                   |                                                                                                           | REV<br>P2                                |                    |  |