


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	K2	REVISED PER ECR-25-255998	11SEP2025	SA	DSC

AMP WIRE RANGE	 Listed FILE E13288
12-10 AWG SOLID OR STRANDED	12-10 AWG STRANDED

- 1
- STAMP 8S AMP 12-10* APPROX AS SHOWN
- 2
- WIRE INSULATION DIAMETER:
ø3.810[.150] TO ø6.350[.250]
- 3
- BODY MATRIAL THK: 1.016±0.051[.040±.002]
- 4
- MATERIAL: BODY - BRASS PER ASTM B36
INSULATION - PVC.
- 5
- APPLIES FROM EDGE OF METAL WIRE BARREL TO
CENTER OF STUD HOLE
- 6
- DIMPLE STAMP MARK OPTIONAL
- 7
- FINISH:
BODY - TIN PLATE 0.00254[.000100]
MIN EXT THK PER ASTM B545
INSULATION COLOR - YELLOW



1 KIT = 100 PIECES	LOOSE PIECE	6-53247-0
2500	ON TAPE, REEL	53247-2
500	LOOSE PIECE	53247-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]		THIS DRAWING IS A CONTROLLED DOCUMENT.			TE TE Connectivity																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600V MAX (1000V FIXTURE OR SIGN)		DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -		DWN L OLMEDA 26JUN95		NAME TERMINAL, SPRING SPADE, SHORT, PLASTI-GRIP, WIRE SIZE: 12-10 AWG																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																	
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] SOLID OR STRANDED		MATERIAL 4	FINISH 7	CHK M ELLIS 26JUN95																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																				
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				APVD G NGO 26JUN95																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																					
								PRODUCT SPEC UL 486A-B																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																			</