


TECHNICAL DATA	T411351X02X-000	T411351X03X-000	T411351X04X-00X	T411351X05X-000
RATED VOLTAGE	250V	250V	250V	60V
RATED CURRENT	4A	4A	4A	4A
POLLUTION DEGREE	3	3	3	3
OVERVOLTAGE CATEGORY	II	II	II	II
CONTACT RESISTANCE	≤10mΩ	≤10mΩ	≤10mΩ	≤10mΩ
INSULATION RESISTANCE	>100MΩ	>100MΩ	>100MΩ	>100MΩ
DEGREE OF PROTECTION	IP67	IP67	IP67	IP67
OPERATION TEMPERATURE	-40~85°C	-40~85°C	-40~85°C	-40~85°C



T4113512041-001	RPC-M12D-MR-4CON-PG9-SHU-LN
T4113512051-000	RPC-M12D-MR-5CON-PG9-SHU
T4113511051-000	RPC-M12D-MR-5CON-PG7-SHU
T4113512052-000	RPC-M12D-MR-5CON-PG9-SH
T4113511052-000	RPC-M12D-MR-5CON-PG7-SH
T4113512041-000	RPC-M12D-MR-4CON-PG9-SHU
T4113511041-000	RPC-M12D-MR-4CON-PG7-SHU
T4113512042-000	RPC-M12D-MR-4CON-PG9-SH
T4113511042-000	RPC-M12D-MR-4CON-PG7-SH
T4113512031-000	RPC-M12D-MR-3CON-PG9-SHU
T4113511031-000	RPC-M12D-MR-3CON-PG7-SHU
T4113512032-000	RPC-M12D-MR-3CON-PG9-SH
T4113511032-000	RPC-M12D-MR-3CON-PG7-SH
T4113512021-000	RPC-M12D-MR-2CON-PG9-SHU
T4113511021-000	RPC-M12D-MR-2CON-PG7-SHU
T4113512022-000	RPC-M12D-MR-2CON-PG9-SH
T4113511022-000	RPC-M12D-MR-2CON-PG7-SH
TE PN	TYPE


NOTE:
1. MATERIAL:
ITEM NO.1:NUT -ZINC DIE-CAST,NICKEL PLATED
ITEM NO.2:HOUSING -PA
ITEM NO.3:CONTACT -BRONZE
ITEM NO.4: HOUSING BODY: -BRASS
2. CONTACT FINISH:
GOLD OVER NICKEL OR SILVER OVER NICKEL
3. CABLE WIRES:
24AWG/0.25mm²...18AWG/0.75mm² (WITHOUT FERRULE)
26AWG/0.14mm²...20AWG/0.50mm² (WITH FERRULE)
4. ALLDIMENSIONS ARE FOR NOMINAL REFERENCE ONLY UNLESS OTHERWISE STATED
5. PACKAGEING: 1PIECE IN A BAG
6. PN INFORMATION

T411351XXXX-000

CONTACT FINISH:
1: GOLD OVER NICKEL
2: SILVER OVER NICKEL

NUMBERS OF PINS:
02: 2 PINS
03: 3PINS
04: 4 PINS
05: 5PINS
08: 8 PINS

CABLE OUTLET:
1: PG7(CABLE FEED: 4-6mm)
2: PG9(CABLE FEED: 6-8mm)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Nick Pan 24AUG2015		 TE Connectivity															
		CHK Kobby Zhao 24AUG2015																	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME M12 MALE, RIGHT ANGLE SHIELDED CONNECTOR D CODE, SCREW TERMINAL		SIZE CAGE CODE DRAWING NO RESTRICTED TO													
		APVD Xiang Xu 24AUG2015																	
		PRODUCT SPEC 108-106140																	
		APPLICATION SPEC 114-137144																	
MATERIAL		FINISH		WEIGHT		A2		-		C-T411351XXXX000		-							
-		-		-		Customer Drawing		SCALE		2:1		SHEET		1 OF 1		REV		B1	
-		-																	