


P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	ECR-15-017530	02DEC2015	GY	CW
	B2	ECR-16-015492	12NOV2016	QY	CW
	C	ECR-21-105750	01JUL2021	BS	CW
	D	ECR-25-246911	26JUN2025	ABS	RB





- NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
 2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T20200X20XX000)

- 注释:
1. 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 4 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线类型: 冷压接
 2. 端子需要单独订购.
(订货号参考图面: T20200X20XX000)




4X M3 SCREW RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐锁紧力矩0.5Nm

M4 SCREW RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4 螺丝, 推荐锁紧力矩1.2Nm




TYPE-1, T2020642201-000, TE LOGO
类型-1, T2020642201-000, TE LOGO

TYPE-2, T2020642201-001, STAINLESS STEEL SCREW, TE LOGO
类型-2, T2020642201-001, 不锈钢螺丝, TE LOGO



PANEL CUT FOR INSERTS FOR USE
WITHOUT HOODS/ HOUSINGS
不用防护外壳时芯件的安装开孔图

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN David Wang 30OCT2014	 TE Connectivity						
		CHK Chris Wang 30OCT2014							
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD Xiang Xu 30OCT2014	NAME HD-064-F						
	0 PLC ±-	PRODUCT SPEC 108-137042	SIZE A3				CAGE CODE 00779	DRAWING NO C-T2020642201000	RESTRICTED TO -
	1 PLC ±-	APPLICATION SPEC 114-137042							
	2 PLC ±-	WEIGHT -							
3 PLC ±-									
4 PLC ±-									
ANGLES ±-									
MATERIAL - -	FINISH - -								
CUSTOMER DRAWING			SCALE 1:1		SHEET 1 OF 2		REV D		





REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


NOTE:

SEE SHEET 1

注释:
见页 1




TYPE-3, T2020642201-002, STAINLESS STEEL SCREW, NO LOGO
类型-3, T2020642201-002, 不锈钢螺丝, 无LOGO



ALL DIMENSIONS ARE SAME AS TYPE 1,
EXCEPT THOSE DEFINED IN THIS TYPE.
除了在本类型中定义的尺寸外, 其它尺寸同类型 1

T2020642201-002	HD-064-F	HD-064 FEMALE INSERT, STAINLESS STEEL SCREW, NO LOGO HD-064 母插, 不锈钢螺丝, 无LOGO	TYPE-3 类 型-3
T2020642201-001	HD-064-F	HD-064 FEMALE INSERT, STAINLESS STEEL SCREW HD-064 母插, 不锈钢螺丝	TYPE-2 类 型-2
T2020642201-000	HD-064-F	HD-064 FEMALE INSERT HD-064 母插	TYPE-1 类 型-1
PART NUMBER 料 号	PART DESCRIPTION 描 述		TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN David Wang 30OCT2014	 TE Connectivity			
DIMENSIONS: mm		CHK Chris Wang 30OCT2014	NAME HD-064-F			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Xiang Xu 30OCT2014				
		PRODUCT SPEC 108-137042	SIZE A3			
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		APPLICATION SPEC 114-137042				
MATERIAL - -		FINISH - -	WEIGHT -	CAGE CODE 00779	DRAWING NO C-T2020642201000	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 1:1	SHEET 2 OF 2	REV D