





REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F4	REVISED PER ECN-25-360726	19JAN2026	CM	RE
	F3	REVISED PER ECR-16-015552	3NOV16	DL	T.D

SECT.
断面 A-ASECT.
断面 B-B

この寸法は嵌合力によって規定する。
THIS DIMENSION IS CONTROLLED
WITH MATING FORCE

断面 C-C

NOTE;

1. THE MATING TAB P/N 170256, 170257
(FOR MULTIPLE Pos.)



REVERSE REEL

STRESS RELIEVING



SEPARATE PAPER TYPE

FINISH IS SUBJECT TO CHANGE BY THE TYPE OF
STRESS RELIVING PROCESS
INERT GAS FURNACE- - - -MATTE
ATMOSPHERIC FURNACE FOLLOWED BY ACID PICKLE- - - -BRIGHT SECT.

注記:

1. 嵌合する相手タブは型番170256及び170257で多極用として使用される。
2. 逆巻きリール
3. ストレス除去処理
処理法により外観が変わります。
不活性ガス加熱方式-無光沢
大気加熱方式-光沢

2. OBSOLETE

4. TIN PLATING

2. OBSOLETE

TIN PLATING

鍍めつき

FINISH 仕上

BRASS THICKNESS 黄銅板厚0.32

MATERIAL 材質

PART NO. 型番

抱合電線切断面積(WIRE RANGE)
2-3. 37 mm² (AWG-14-12)

被覆外径(INSULATION DIA.)
2.9-3.8 mmφ

DIMENSIONS:
単位: ㎜

DWN Y.YAMADA

03APR2007

MATERIAL

SEE TABLE

FINISH

SEE TABLE

3

CHK MANABA SAKAE

03APR2007

APVD MANABA SAKAE

03APR2007

PRODUCT SPEC

製品規格

APPLICATION SPEC

取付適性規格

WEIGHT

0.000000

NAME
名称

.250 SERIES RECEPTACLE WITHOUT LATCH

.250 シリーズ リセプタクル ラッチなし

SIZE

CAGE CODE

DRAWING NO

番番号

RESTRICTED TO

A4

00779

C-170258

CUSTOMER DRAWING

SCALE

1:1

SHEET

1 OF 1

REV F4

0 PLC	10以下	±0.2
1 PLC	10を超え30以下	±0.25
2 PLC	30を超え100以下	±0.3
3 PLC	100以下	±0.3
4 PLC	角度	±3°
ANGLES		±

