



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J	REVISED PER ECN-25-327976	19JUN2025	SP	PD



WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 4801, ET SEQ.).



<u>BODY:</u> COPPER ASTM-B187 ANNEALED TIN PLATE .00381[.000150] MIN THICK PER ASTM B 545	134593-1
<u>INSERT & FUNNEL:</u> BRASS ASTM B36 NICKEL PLATE SAE AMS QQ-N-290A, DATED JULY 2000,.00254 [.000100] MIN THICK	
MATERIAL & FINISH	PART NO.

1. WIRE INSULATOR : 10.8[.425] TO 11.9[.469]
2. WIRE CMA: 83700 TO 119500
3. THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS
4. WEIGHT: 55 GRAMS
5. SEE TE CONNECTIVITY INSTRUCTION SHEET 408-2281 FOR TOOLING AND CRIMP INSTRUCTIONS, FIGURE 2 FOR WIRE STRIPPING DETAIL.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G.ROBERT MAI 89	 TE Connectivity		
		CHK G.ROBERT 16-JAN-97			
		APVD G.ROBERT 16-JAN-97	NAME SEALED COPALUM		
		PRODUCT SPEC —			
		APPLICATION SPEC —			
		WEIGHT 0.000000	SIZE A3	CAGE CODE 00779	DRAWING NO C-134593
CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1	REV J	