

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — BY —

ALL RIGHTS RESERVED.

FIG 11







Diagram dimension	Tolerance
0.99mm max.	±0.1mm
1 – 2.99mm	±0.2mm
3mm min.	±0.3mm





FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING
(BOTTOM VIEW)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	CB ZHOU
-----	---------

CHK	GR, ZHOU
	YN, ZHANG

	XN,ZHANG
APVD	

C.H.HSU
PRODUCT SPEC

—

APPLICATION SPEC



TE Connectivity


OJ-HM2 Cd FREE CUSTOMER DRAWING

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

Λ 3	00779	C=	1721538	—
-----	-------	----	---------	---


SCALE	5:1	SHEET	1 OF 3	REV	5
-------	-----	-------	--------	-----	---

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



1-1721538-9	OJ-SS-124HM2	FIG11	24V	OJ-SS-124HM2	S
1-1721538-8	OJ-SS-112HM2	FIG11	12V	OJ-SS-112HM2	R
1-1721538-7	OJ-SS-112HM2	FIG1	12V	OJ-SS-112HM2	Q
1-1721538-6	OJ-SH-148HM2	FIG11	48V	OJ-SH-148HM2	P
1-1721538-5	OJ-SH-124HM2	FIG11	24V	OJ-SH-124HM2	O
1-1721538-4	OJ-SH-118HM2	FIG11	18V	OJ-SH-118HM2	N
1-1721538-3	OJ-SH-112HM2	FIG11	12V	OJ-SH-112HM2	M
1-1721538-2	OJ-SH-109HM2	FIG11	9V	OJ-SH-109HM2	L
1-1721538-1	OJ-SH-106HM2	FIG11	6V	OJ-SH-106HM2	K
1-1721538-0	OJ-SH-105HM2	FIG11	5V	OJ-SH-105HM2	J
1721538-9	OJ-SH-103HM2	FIG11	3V	OJ-SH-103HM2	I
1721538-8	OJ-SS-148HM2	FIG11	48V	OJ-SS-148HM2	H
1721538-7	OJ-SS-124HM2	FIG11	24V	OJ-SS-124HM2	G
1721538-6	OJ-SS-118HM2	FIG11	18V	OJ-SS-118HM2	F
1721538-5	OJ-SS-112HM2	FIG11	12V	OJ-SS-112HM2	E
1721538-4	OJ-SS-109HM2	FIG11	9V	OJ-SS-109HM2	D
1721538-3	OJ-SS-106HM2	FIG11	6V	OJ-SS-106HM2	C
1721538-2	OJ-SS-105HM2	FIG11	5V	OJ-SS-105HM2	B
1721538-1	OJ-SS-103HM2	FIG11	3V	OJ-SS-103HM2	A
TE PART NO	DESCRIPTION	FIG	PART B	PART A	TYPE

RELAY TYPE

- NOTES:
- 1.TERMINAL DIMENSION BEFORE TINNING.
 - 2.LOT NO. SYSTEM AS FOLLOWING:

 - 3.TERMINAL DIMENSION IS BEFORE SOLDER DIP;
 - 4.FOR THE TIN-PLATING OF THE PINS:
+0.1mm FOR WIDTH,THICKENSS AND DIAMETER.
+0.5mm FOR LENGTH.
 - 5.MARKING FROM INK TO LASER AND USING WELDEDD CONTACT
 - 6.ADD LOT NO. SYSTEM AS FOLLOWING;

- I, DIGITS FOR DAY OF THE WEEK
1...MONDAY IN THIS WEEK;
2...TUESDAY IN THIS WEEK;
.....
7...SUNDAY IN THIS WEEK
II, DIGITS FOR SHIFT OF THE DAY
1...DAY SHIFT IN THIS DAY;
2...NIGHT SHIFT IN THIS DAY;
III, ONE CHARACTER DISTINGUISH THE LINE IDENTITY, SUCH AS: A,B,....Z

		UV RESIN	UV SEAL	16
		EPOXY RESIN	SEAL (BASE & BOBBIN)	15
94V-0		3UEW	MAGNETIC WIRE	14
94V-0		P.B.T	CASE (WHITE)	13
94V-0		P.B.T	BASE	12
94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
94V-0		P.P.S	CARD	9
		Ag ALLOY	MOVABLE CONTACT	8
		Ag ALLOY	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	PBP	NO.TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	GR,ZHOU	—	 TE Connectivity			
		CHK	XN,ZHANG	—				
		APVD	C.H.HSU	—				
		PRODUCT SPEC	—	—				
		APPLICATION SPEC	—	—	OJ-HM2 Cd FREE CUSTOMER DRAWING			
		WEIGHT	0	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		CUSTOMER DRAWING			A3	00779	C-1721538	—
					SCALE	SHEET		REV
					5:1	2 OF 2		F5