






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	PI	PART STATUS CHANGE TO DISCONTINUANCE	09JUN2026	NS	PS



1776113-3 AS SHOWN

- 1

MATERIALS AND FINISH:
HOUSING: HIGH TEMPERATURE POLYAMIDE, UL 94V-0 RATED,
COLOR: BLACK.
TERMINAL: COPPER ALLOY, TIN PLATED.
CLAMP: COPPER ALLOY, NICKEL PLATED.
CLAMPING SCREW: COPPER ALLOY, NICKEL PLATED.
2. WIRE SIZE RANGE: 16-28 AWG.
3. CURRENT RATING: 12A, 150V
OPERATING TEMPERATURE: -40°C TO +110°C
4. SUITABLE FOR 2.4mm MAX PC BOARD THICKNESS.



RECOMMENDED PC BOARD LAYOUT

OBSOLETE	3.5	45.72	12	3-1776113-2
		41.91	11	3-1776113-1
		38.10	10	3-1776113-0
		34.29	9	2-1776113-9
		30.48	8	2-1776113-8
		26.67	7	2-1776113-7
		22.86	6	2-1776113-6
		19.05	5	2-1776113-5
		15.24	4	2-1776113-4
		11.43	3	2-1776113-3
OBSOLETE	2.6	7.62	2	2-1776113-2
OBSOLETE		45.72	12	1-1776113-2
OBSOLETE		41.91	11	1-1776113-1
		38.10	10	1-1776113-0
		34.29	9	1776113-9
		30.48	8	1776113-8
		26.67	7	1776113-7
		22.86	6	1776113-6
		19.05	5	1776113-5
		15.24	4	1776113-4
	11.43	3	1776113-3	
	7.62	2	1776113-2	
DIM A	L	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 02JUN2005	TE Connectivity	
DIMENSIONS: mm		CHK C. RICHARD 02JUN2005		
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±0.000 4 PLC ±0.0000 ±- ANGLES FINISH	APVD C. RICHARD 02JUN2005	NAME TERMINAL BLOCK, PCB MOUNT, STRAIGHT, 8.5mm PROFILE, SIDE WIRE ENTRY, 3.81mm PITCH	
		PRODUCT SPEC -	SIZE A2	CAGE CODE 00779
MATERIAL 		APPLICATION SPEC -	DRAWING NO C-1776113	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 6:1	SHEET 1 OF 1
			REV PI	