

CABTITE EP A 24/14 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Cabtite - Cable Entry Plates**

Insert cables and wires without plugs into control cabinets, enclosures or machines in the smallest of spaces, easily and in a space-saving manner.

With the Cabtite cable entry plates, you can do this even in harsh environments, whether protective hoses, pneumatic/hydraulic hoses or fiber optic cables - you can install your cables quickly, easily and in a space-saving manner. The installation is done through only one rectangular wall cut-out and is therefore up to 40% faster in the installation time (compared to standard cable glands).

The tool less IP54 snap version of cable entry plates are tested according to DIN EN 60529 and made of UL94 V-0 certified TPE material, suitable for the temperature range from -40°C to +90°C.

Cabtite cable entry plates are an economical alternative to conventional cable glands.

General ordering data

Version	Cable entry plate, Cabtite (cable entry system), TPE, grey, Height: 44 mm, Width: 142 mm, Depth: 12 mm, -40 °C...90 °C, IP54
Order No.	2743550000
Type	CABTITE EP A 24/14 GY
GTIN (EAN)	4064675 12097 1
Qty.	10 pc(s).

CABTITE EP A 24/14 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	12 mm	Depth (inches)	0.472 inch
Height	44 mm	Height (inches)	1.732 inch
Width	142 mm	Width (inches)	5.591 inch
Wall thickness, min.	1.5 mm	Wall thickness, max.	2.5 mm
Net weight	45.3 g		

Temperatures

Operating temperature	-40 °C...90 °C
-----------------------	----------------

General information

Material	TPE	Protection class (UL)	Type 1, Type 12
Protection degree	IP54	Silicone	No
UL 94 flammability rating	V-0		

Number of connectable cables

Type of mounting	Snap-on								
Number of connectable cables	14								
Cable entries	<table> <tr> <td>Number</td><td>14</td></tr> <tr> <td>Cable diameter, min.</td><td>1 mm</td></tr> <tr> <td>Cable diameter, max.</td><td>12.1 mm</td></tr> <tr> <td>Cable type</td><td>Round cable</td></tr> </table>	Number	14	Cable diameter, min.	1 mm	Cable diameter, max.	12.1 mm	Cable type	Round cable
Number	14								
Cable diameter, min.	1 mm								
Cable diameter, max.	12.1 mm								
Cable type	Round cable								

Classifications

ETIM 6.0	EC002624	ETIM 7.0	EC002624
ETIM 8.0	EC002624	ETIM 9.0	EC002624
ETIM 10.0	EC002624	ECLASS 9.0	27-18-28-15
ECLASS 9.1	27-18-92-65	ECLASS 10.0	27-18-28-15
ECLASS 11.0	27-18-28-15	ECLASS 12.0	27-18-28-15
ECLASS 13.0	27-18-28-15	ECLASS 14.0	27-18-28-15
ECLASS 15.0	27-18-28-15		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E223801

CABTITE EP A 24/14 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity

[EU Declaration of Conformity - Cabtite EP - DoC DE PS2483](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[INSTR CABTITE EP DE/EN](#)

Catalogues

[Catalogues in PDF-format](#)

CABTITE EP A 24/14 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

