


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED PER ECO-19-013549	04SEP2019	BKW	GJ
	A1	REVISED PER ECR-20-100211	06AUG2020	JP	VS
	A2	REVSIED PER ECR-21-107670	20JUL2021	SS	VS







1 MATERIAL MARK

2. WIRE RANGE: 14-16 AWG COPPER STRANDED.

3. INSULATION RANGE: 2.3~3.5

4. SUPPLIED CONTINUOUS ON REELS.

5 PRELIMINARY - NOT FOR PRODUCTION



SECTION B - B

M0	HIGH CONDUCTIVE COPPER ALLOY	HIGH TEMP (140°C)	 2329916-2
M2	COPPER ALLOY	STANDARD TEMP (105°C)	2329916-1
MATERIAL MARK 	MATERIAL	TEMPERATURE RATING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 27APR2018 B. WEAVER CHK 27APR2018 S. FERNANDES APVD 27APR2018 C. YI		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.40 2 PLC ±0.30 3 PLC ± 4 PLC ± ANGLES ±		NAME POWER VERSA-LOCK REC TERMINAL WIRE SEAL 14-16 AWG -	
MATERIAL -		PRODUCT SPEC 108-143081 APPLICATION SPEC 114-143082		SIZE A2	CAGE CODE -
FINISH -		WEIGHT -		DRAWING NO C-2329916	
SEE TABLE		PRE-PLATED Sn		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 5:1	SHEET 1 of 1
				REV A2	