



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REVISED PER ECR-26-282233	30JUN2026	GSK	MP



- 1 BODY MATERIAL THK 0.991±0.051[.039±.002]
- 2 FOR Ø6.502[Ø.256] MAX WIRE INS.
- 3 STAMP AMP 8* 14 APPROX AS SHOWN.
- 4 MATERIAL:
BODY – COPPER PER ASTM B152
INSULATION – NYLON
- 5 FINISH:
BODY – TIN PLATE .000100 [0.00254]
MIN EXT PER ASTM B545
INSULATION – RED

100	LOOSE PC	324045
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F]		THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN S.S. GOULDEN 6-18-93 CHK R. HERSEY 6-18-93 APVD B. BARE 6-18-93 PRODUCT SPEC 108-162357 APPLICATION SPEC — WEIGHT CUSTOMER DRAWING <td colspan="3"> TE TE Connectivity </td>			TE TE Connectivity					
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: —		DIMENSIONS: mm [INCHES] 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.127[.005] 4 PLC ± — ANGLES ± —		NAME TERMINAL, RING TONGUE, TERMINYL WIRE SIZE: 8 AWG						
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 6.64-10.5mm² [13,100-20,800] STRANDED									SIZE A3		CAGE CODE 00779	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL 		FINISH 		SCALE NTS			SHEET 1 OF 1		REV E	