





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C7	PART STATUS CHANGE TO DISCONTINUANCE	07JUL2026	NS	PS




NOTES

1. MATERIALS AND FINISH:
HOUSING: PA 6-6, UL 94-V0, COLOR: GREEN.
CLAMP: COPPER ALLOY, NICKEL PLATED.
CONTACT SPRING : COPPER ALLOY, FINISH: SEE TABLE
CLAMPING SCREW: M3, COPPER ALLOY, NICKEL PLATED.
2. MECHANICAL
MAX. INSERTION FORCE PER HOLE : 3N
MIN. WITHDRAWAL FORCE PER HOLE: 1.5N
WIRE STRIPPING LENGTH : 6-7.5 mm
RECOMMENDED/ HIGHEST TIGHTENING TORQUE : 0.5/0.6 Nm
3. ELECTRICAL
WIRE RANGE : 30 - 12 AWG
MAX. VOLTAGE : 300 V
MAX. CURRENT : 15 A
CONTACT RESISTANCE : <15 m Ohm
INSULATION RESISTANCE : >1000 M Ohm (500V DC)
4. OPERATING TEMPERATURE RANGE: -40 °C TO +110 °C

- | | |
|---|--|
|  | TOLERANCE NOT CUMULATIVE. |
|  | NOTE DELETED |
|  | SPECIAL MARKING TO BE PERMANENT BLACK LETTERING |
|  | SPECIAL MARKING TO BE IN PERMANENT BLACK INK |
|  | SPECIAL MARKING TO BE IN PERMANENT WHITE INK (SEE BACKGROUND COLOUR) |




POLARIZATION KEY SLOT




	DETAIL J	40.64	8	3-284041-4	
	DETAIL H	OBSOLETE	20.32	4	3-284041-3
	DETAIL G	OBSOLETE	30.48	6	3-284041-2
	DETAIL F	OBSOLETE	30.48	6	3-284041-1
	DETAIL E	OBSOLETE	40.64	8	3-284041-0
	DETAIL D		20.32	4	2-284041-9
	DETAIL C	OBSOLETE	20.32	4	2-284041-8
	DETAIL B	OBSOLETE	20.32	4	2-284041-7
	DETAIL A	OBSOLETE	20.32	4	2-284041-6
		OBSOLETE	127.00	25	2-284041-5
		OBSOLETE	121.92	24	2-284041-4
		OBSOLETE	116.84	23	2-284041-3
		OBSOLETE	111.76	22	2-284041-2
		OBSOLETE	106.68	21	2-284041-1
		OBSOLETE	101.60	20	2-284041-0
		OBSOLETE	96.52	19	1-284041-9
		OBSOLETE	91.44	18	1-284041-8
		OBSOLETE	86.36	17	1-284041-7
			81.28	16	1-284041-6
		OBSOLETE	76.20	15	1-284041-5
			71.12	14	1-284041-4
		OBSOLETE	66.04	13	1-284041-3
			60.96	12	1-284041-2
			55.88	11	1-284041-1
			50.80	10	1-284041-0
			45.72	9	284041-9
			40.64	8	284041-8
			35.56	7	284041-7
			30.48	6	284041-6
			25.40	5	284041-5
			20.32	4	284041-4
			15.24	3	284041-3
			10.16	2	284041-2
			DIM. A	NO OF POS.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 27MAR2001 ZANOLINI		 TE Connectivity	
DIMENSIONS:		CHK 27MAR2001 D. BIEVENDOR			
mm	TOL. EXANCES UNLESS OTHERWISE SPECIFIED:	APP'D 27MAR2001 D. BIEVENDOR		NAME	
	0 PLC ±0.3	PRODUCT SPEC		TERMINAL BLOCK, VERTICAL PLUG	
	2 PLC ±0.25	APPLICATION SPEC		STACKING, LEFT HAND	
	3 PLC ±0.3			5.08mm PITCH	
	4 PLC ±0.3			SIZE	CAGE CODE
MATERIAL	ANGLES ±0.2°			DRAWING NO	
	FINISH	WEIGHT		RESTRICTED TO	
-	-	CUSTOMER DRAWING		A 00779 C-284041	
				SCALE	5:1
				SHEET	1 of 2
				REV C	




DETAIL A


KEY




DETAIL B




DETAIL C




DETAIL D




DETAIL E




DETAIL F



DETAIL G



DETAIL H



DETAIL J