



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED PER ECO-19-002730	02AUG2019	A.S	H.L

D

C


B

A




NOTES:



- ⚠ MATERIAL CONTACT: PHOSPHORBRONZE
MATERIAL HOUSING: GLASSFILLED POLYESTER
UL-RATING 94V0 (GRAY).
- ⚠ GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT):
1,27μm NICKEL MIN. AND ACTION PIN: 0,5μm TIN MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
- ⚠ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2.
- ⚠ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 1.
- ⚠ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE
QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
- ⚠ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE
QUALITY LEVEL III, UNCONTROLLED ENVIRONMENT APPLICATIONS.
- ⚠ CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE
APPROVED LUBRICANT.
- ⚠ CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE.
- ⚠ PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID (110 HOLES).
- ⚠ HOLES IN ROW f AND z FOR POSSIBLE FUTURE USE OF
GROUND RETURN SHIELD. (SHIELDS NOT YET TOOLED)
- ⚠ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



P.C.B. HOLE DIM. ACTION PIN
FOR DETAILS SEE
APPLICATION SPECIFICATION



SECTION A-A



OBSOLETE	⚠6⚠	⚠	1-5352268-9
	⚠5⚠	⚠	-5352268-9
	⚠4⚠	⚠	-5352268-4
	⚠3⚠	⚠	5352268-1
FINISH		MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.N.KIRAN	23AUG2004	TE TE Connectivity	
DIMENSIONS: mm		CHK B.MOOIJ	27OCT2004		
		APVD B.MOOIJ	27OCT2004	NAME Z-PACK 2mm HM TYPE B 110 POS. 22 COLUMNS VERTICAL FEMALE CONNECTOR ASSEMBLY	
		PRODUCT SPEC 108-19082	APPLICATION SPEC 114-19029		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT 0.000000	SCALE 5:1	SHEET 1 of 1	REV F
MATERIAL -		CUSTOMER DRAWING		RESTRICTED TO -	
		FINISH -			