





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J	REVISED PER ECR-25-265843	14APR2026	DK	JP



- 1 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
2. WIRE RANGE: 0.05 – 0.15mm²(30-26 AWG).
- 3 0.00130 [0.000050] MIN THK NICKEL OVERALL , AND 0.00254 [.000100] MIN THK MATTE TIN IN LOCALIZED TIN PLATE AREA, AND 0.00076 [0.000030] MIN THK GOLD OR 0.00008 [0.000003] GOLD FLASH OVER 0.00068 [0.000027] MIN THK PdNi STRIPES PER TE CONNECTIVITY'S DISCRETION IN LOCALIZED GOLD PLATE AREA.



SECTION A-A
SCALE 20:1



SECTION B-B
SCALE 20:1

3	0.20 [.008] BRASS	1-770835-0
1	0.20 [.008] BRASS	770835-3
PRE-TIN	0.20 [.008] BRASS	770835-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 05MAR03	 TE Connectivity				
		CHK C. JONES 05MAR03					
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C. JONES 05MAR03	NAME PIN MINI UNIVERSAL MATE-N-LOK(TM)				
	0 PLC ± -	PRODUCT SPEC					
	1 PLC ± -	—					
	2 PLC ± 0.13[.005]	APPLICATION SPEC					
	3 PLC ± -	—					
	4 PLC ± -	—					
	ANGLES ± -	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
MATERIAL —	FINISH —	WEIGHT 0.000000	A2	00779	C=770835	—	
CUSTOMER DRAWING					SCALE 10:1	SHEET 1 of 1	REV J