



VERTICALLY POLARIZED OMNI ANTENNAS

OD9

860-960 MHZ VERTICALLY POLARIZED OMNI-DIRECTIONAL ANTENNA

The NLOS series omni-directional antenna system are constructed of UV stabilized fiberglass and stainless steel for long service life. Mounting is easy with a dual u-bolt mounting system. The antennas are vertically polarized. The 6dBi and 8dBi come standard with 18" pigtails terminated in an N female connector. The 5dBi and 11dBi comes standard with an integrated N Female connector. The omni's are DC grounded for lightning protection. The 11dBi omni is available with 1 deg electrical downtilt which provides null fill and improved close-in coverage.

FEATURES

- 900MHz omni-directional antenna
- Available in 5, 6, 8 and 11dBi gain models
- 1 degree electrical downtilt available on the 11dBi model
- UV stabilized fiberglass / stainless steel construction
- 18" pigtail with type N female connector standard (6dBi and 8dBi models only)

MARKETS


- 900 MHz ISM band applications
- WISP base station equipment
- Non line-of-sight applications
- Cellular applications

PARAMETER	OD9-5	OD9-6	OD9-8	OD9-11D1
VSWR	1.5:1	1.5:1	1.5:1	1.5:1
Impedance	50 ohm	50 ohm	50 ohm	50 ohm
Input power	100W	100W	100W	100W
Pole diameter (OD)	1" - 2" (25-51mm)	1" - 2" (25-51mm)	1" - 2" (25-51mm)	1" - 2" (25-51mm)
Operating temperature	-45 - +70°C	-45 - +70°C	-45 - +70°C	-45 - +70°C
Rated wind velocity	125 mph (56 m/sec)	125 mph (56 m/sec)	125 mph (56 m/sec)	125 mph (56 m/sec)
Gain	5dBi	6dBi	8dBi	11dBi
VSWR 1.5:1 bandwidth	890-950 MHz	865-945 MHz	865-945 MHz	860-960 MHz
VSWR 2.0:1 bandwidth		860-960 MHz	860-960 MHz	
Vertical 3dB beamwidth	36°	16°	10°	7°

PARAMETER	OD9-5	OD9-6	OD9-8	OD9-11D1
Electrical downtilt	0	0	0	1
Length	28.74 in (730 mm)	5.6 ft (1.7 m)	8.5 ft (2.6 m)	11 ft°(3.4 m)
Diameter	0.83 in (21 mm)[At Mounting]	1.5 in (38 mm)	1.5 in (38 mm)	1.5 in (38 mm)
IP Rating	IP66	IP55	IP55	IP65

SYSTEM ORDERING

OD9-5	5dBi slimline NLOS series 900MHz omni antenna with N female bulkhead connector
OD9-6	6dBi NLOS series 900MHz omni antenna with 18" pigtail / N female connector
OD9-8	8dBi NLOS series 900MHz omni antenna with 18" pigtail / N female connector
OD9-11D1	11dBi 1deg elec downtilt NLOS series 900MHz omni antenna with integrated N female connector



TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, complete, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE EXPRESSLY DISCLAIMS ALL IMPLIED WARRANTIES REGARDING THE INFORMATION CONTAINED HEREIN, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. In no event will TE be liable for any direct, indirect, incidental, special or consequential damages arising from or related to recipient's use of the information. It is the sole responsibility of recipient of this information to verify the results of this information using their engineering and product environment. Recipient assumes any and all risks associated with the use of the information. Antenna performance may vary. TE is a component manufacturer, and customer and/or end-user is responsible for all end-use compliance and regulatory requirements. These marketing materials do not constitute an offer or agreement of sale, and TE Connectivity shall be bound by and subject to only those terms and conditions set forth in a written agreement referencing specific products and signed by an authorized representative of TE.

©2026 TE Connectivity. All Rights Reserved.

05/26 Original