


printed on 16 Mar 2023 08:35 (China Standard Time) from F6086105

© 2023 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	REVISED PER ECN-23-203008	15MAR2023	IT	SZ



NOTES:

UNLESS OTHERWISE SPECIFIED

- 1 MATERIAL: 6063 ALUMIMUM.
- 2 FINISH: ANODIZATION, NATURAL.
3. 0,2mm MAX BURR.
4. VARIATION IN PLATING COLOR IS NORMAL AND ALLOWED.
- 5 MAXIMUM PIN LEAN OF 8° IN ANY DIRECTION.
6. RoHS COMPLIANT AND CERTIFIED.
- 7 FINISH: HARD ANODIC COATING PER MIL-A-8625 TYPE III,
40.64 MICROMETERS MINIMUM THICK.



7	1829905-4
2	1829905-2
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.TAO 6-26-06	TE Connectivity			
DIMENSIONS: mm		CHK V.KHEIL 7-13-06				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME HEAT SINK SFP DWDM 13.5mm TALL			
0 PLC ±.2 1 PLC ±.2 2 PLC ±.10 3 PLC ±.08 4 PLC ±0.0001 ANGLES ±5		PRODUCT SPEC -	SIZE A260779			
MATERIAL material_2		APPLICATION SPEC -	CAGE CODE C-1829905			
FINISH finish_spec_2		WEIGHT -	DRAWING NO 1829905			
		CUSTOMER DRAWING	SCALE 4.000		SHEET 1 OF 1	REV C3