
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	22JAN2016	NK	RH



1 WORKING TEMPERATURE: 105° C

2 VOLTAGE: 300V MAX.

3 COLOR: BLUE

4 WIRE RANGE: #22–#14AWG. MAX.3#16 MIN.2#22

5 SPRING INSERT: STEEL

2299501–1 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± 0.2[.007]
2 PLC	± 0.4[.015]
3 PLC	± –
4 PLC	± –
ANGLES	± –

MATERIAL: TOUGH THERMOPLASTIC UL 94V–2 FLAME–RETARDANT

FINISH: –

DWN NAGALAKSHMI K 22JAN2016
CHK HILL RYAN 22JAN2016
APVD HILL RYAN 22JAN2016
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

CUSTOMER DRAWING

TE Connectivity

NAME: CPGI–WC–WG–BL–BULK

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C–2299501	—

SCALE 3:1 SHEET 1 OF 1 REV A