




LOCKING UNIT POSITION UPPER
CABLE OUTLET POSITION 1






LOCKING UNIT POSITION UPPER
CABLE OUTLET POSITION 2



FLAPS OPEN LEFT




FLAPS OPEN RIGHT



0- -3 AS SHOWN
wie dargestellt

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A1		NOTE 5 ADDED	17NOV2021	YP	GL
A2		REVISED PER PCN-23-178661	15JUN2023	MK	GL
A3		DRAWING UPDATE	24FEB2025	RK	GL
C		REVISED PER PCN-26-270464	10FEB2026	MK	GL



SECTION A-A

WIRING SCHEDULE:
Belegungsplan:

CAVITY-NO.	IDENTIFICATION	WIRE COLOUR	WIRE SECTION
1	L1	BROWN	6mm ² (ITEM 17)
2	L2	BLACK	6mm ² (ITEM 17)
3	L3	GREY	6mm ² (ITEM 17)
4	N	BLUE	6mm ² (ITEM 17)
5	GROUND/EARTH	GREEN/YELLOW	25mm ² (ITEM 19)
8	DC+	ORANGE	70mm ² (ITEM 18)
9	DC-	ORANGE	70mm ² (ITEM 18)

LENGTH SCHEDULE:
Laengentabelle:

TE PART NO	REV	LENGTH L(mm)	TOL	CABLE OUTLET POSITION	FLAP UNIT
2393949-1	C	1500	+30	POSITION 1	NO FLAPS
2393949-2	C	1500	+30	POSITION 2	NO FLAPS
2393949-3	C	1500	+30	POSITION 1	FLAPS OPEN LEFT
2393949-4	C	1500	+30	POSITION 2	FLAPS OPEN LEFT
2393949-5	C	1500	+30	POSITION 1	FLAPS OPEN RIGHT
2393949-6	C	1500	+30	POSITION 2	FLAPS OPEN RIGHT
1-2393949-1	C	3000	+50	POSITION 1	NO FLAPS
1-2393949-2	C	3000	+50	POSITION 2	NO FLAPS
1-2393949-3	C	3000	+50	POSITION 1	FLAPS OPEN LEFT
1-2393949-4	C	3000	+50	POSITION 2	FLAPS OPEN LEFT
1-2393949-5	C	3000	+50	POSITION 1	FLAPS OPEN RIGHT
1-2393949-6	C	3000	+50	POSITION 2	FLAPS OPEN RIGHT

WIRING SCHEDULE FOR SIGNAL CABLE:
Belegungsplan für Signalkabel:

Pin No.	Identification	Wire colour	Wire Section
1	LED GN	GN	0.5mm ²
2	LED RD	YE	0.5mm ²
3	-	-	-
4	GND LED	BK/OR	0.5mm ²
5	LED WT	WH	0.5mm ²
6	TDC+	OR	0.5mm ²
7	Proxi out	BU	0.5mm ²
8	TDC ground	GY	0.5mm ²
9	TDC-	RD	0.5mm ²
10	T AC	WH/BU	0.5mm ²
11	PE S	BK	0.5mm ²
12	CP out	VO	0.5mm ²

NOTES

1 STRIPPED ONLY OUTER JACKET AND BRAID.
ELECTRICAL TESTING IS ACCORDING APPLICATION SPECIFICATION.


2 APPLICATION SPECIFICATION:
114-94723 CHARGE INLET COMBO 1 IEC 62196-3.

3 CUTTING LENGTHS TO BE FIXED BY MANUFACTURING.

4 MANUFACTURING CODE:
TE PART NO., CURRENT REV. LEVEL AND DATE CODE (DD.MM.YY),
TO BE PRINTED ON LABEL (ITEM 21).
LABEL TO BE APPLIED TO THE CABLE AFTER SUCCESSFUL ELECTRICAL TEST.

5. FLAP ASSY (ITEM 15/16) WILL BE NOT MOUNTED AS SHOWN BUT ATTACHED INTO PACKAGING.

LABEL LEGEND:
Label Beschriftung:



TE PART NO., CURRENT REVISION
TE Teilenummer, aktuelle Revision

PRODUCTION DATE
Produktionsdatum

3m	3m	3m	3m	3m	3m	3m	1.5m	1.5m	1.5m	1.5m	1.5m	1.5m	SIGNAL CABLE	34
3m	3m	3m	3m	3m	3m	3m	1.5m	1.5m	1.5m	1.5m	1.5m	1.5m	SIGNAL CABLE	33
3m	3m	3m	3m	3m	3m	3m	1.5m	1.5m	1.5m	1.5m	1.5m	1.5m	SIGNAL CABLE	32
3m	3m	3m	3m	3m	3m	3m	1.5m	1.5m	1.5m	1.5m	1.5m	1.5m	SIGNAL CABLE	31
3m	3m	3m	3m	3m	3m	3m	1.5m	1.5m	1.5m	1.5m	1.5m	1.5m	SIGNAL CABLE	30
3m	3m	3m	3m	3m	3m	3m	1.5m	1.5m	1.5m	1.5m	1.5m	1.5m	SIGNAL CABLE	29
3m	3m	3m	3m	3m	3m	3m	1.5m	1.5m	1.5m	1.5m	1.5m	1.5m	SIGNAL CABLE	28
3m	3m	3m	3m	3m	3m	3m	1.5m	1.5m	1.5m	1.5m	1.5m	1.5m	SIGNAL CABLE	27
3m	3m	3m	3m	3m	3m	3m	1.5m	1.5m	1.5m	1.5m	1.5m	1.5m	SIGNAL CABLE	26
3m	3m	3m	3m	3m	3m	3m	1.5m	1.5m	1.5m	1.5m	1.5m	1.5m	SIGNAL CABLE	25
3m	3m	3m	3m	3m	3m	3m	1.5m	1.5m	1.5m	1.5m	1.5m	1.5m	SIGNAL CABLE	24
1	1	1	1	1	1	1	1	1	1	1	1	1	12POS,MICRO MNL,RCPT HSG	23
11	11	11	11	11	11	11	11	11	11	11	11	11	TERMINAL MICRO MATE N LOCK	22
1	1	1	1	1	1	1	1	1	1	1	1	1	LABEL, HELL	21
1	1	1	1	1	1	1	1	1	1	1	1	1	CAB TIE, CLIP, HELL-T18R-HR-N46	20
3m	3m	3m	3m	3m	3m	3m	1.5m	1.5m	1.5m	1.5m	1.5m	1.5m	PE H8S CABLE 25 SQMM	19
6m	6m	6m	6m	6m	6m	6m	3m	3m	3m	3m	3m	3m	70 mm ² Huber+Suhrner	18
3m	3m	3m	3m	3m	3m	3m	1.5m	1.5m	1.5m	1.5m	1.5m	1.5m	4X6 mm ² Coroplast	17
1	1	-	-	-	-	-	1	1	-	-	-	-	FLAP, ASSY, INLET COMBO 2, RIGHT	16
-	-	1	1	-	-	-	-	-	1	1	-	-	FLAP, ASSY, INLET COMBO 2, LEFT	15
1	1	1	1	1	1	1	1	1	1	1	1	1	MQS BLINDSTOPFEN	14
1	1	1	1	1	1	1	1	1	1	1	1	1	COVER, CABLE SEAL, COMBO DC	13
1	1	1	1	1	1	1	1	1	1	1	1	1	FAMILY SEAL, COMBO DC	12
1	1	1	1	1	1	1	1	1	1	1	1	1	COVER, CABLE SEAL, AC	11
1	1	1	1	1	1	1	1	1	1	1	1	1	STRAIN RELIEF, AC	10
1	1	1	1	1	1	1	1	1	1	1	1	1	Family Seal, AC	9
1	-	1	-	1	-	1	-	1	-	1	-	-	CABLE EXIT, RECT, COMBO RIGHT	8
-	1	-	1	-	1	-	1	-	1	-	1	-	CABLE EXIT, RECT, COMBO, LEFT	7
2	2	2	2	2	2	2	2	2	2	2	2	2	DIA 6MM,PIN TERMINAL	6
2	2	2	2	2	2	2	2	2	2	2	2	2	SEALING	5
1	1	1	1	1	1	1	1	1	1	1	1	1	PROTECTION CAP CHARGE INLETS	4
1	1	1	1	1	1	1	1	1	1	1	1	1	PIN DIA 6.0,RIGID,POWER PE	3
4	4	4	4	4	4	4	4	4	4	4	4	4	DIA 6MM,PIN TERMINAL	2
1	1	1	1	1	1	1	1	1	1	1	1	1	COMBO 2,CHARGE INLET ASSY, LED	1
1-6	1-5	1-4	1-3	1-2	1-1	0-6	0-5	0-4	0-3	0-2	0-1		DESCRIPTION	ITEM NO.
C	C	C	C	C	C	C	C	C	C	C	C	C	REVISION OF EACH ASSY NO (WHEN BLANK, USE OWN REVISION)	

QTY REQD PER ASSY				PARTS LIST			
THIS DRAWING IS A CONTROLLED DOCUMENT.				12JUL2021			
DIMENSIONS:				CHK M. BLOCK			
mm				APVD G. LINDEMANN			
TOLERANCES UNLESS OTHERWISE SPECIFIED:				PRODUCT SPEC			
0 PLC ±				108-94839			
1 PLC ±				APPLICATION SPEC			
2 PLC ±				114-94723			
3 PLC ±				WEIGHT			
4 PLC ±				CUSTOMER DRAWING			
ANGLES FINISH				SCALE 1:1			
MATERIAL				SHEET 1 OF 1			
-				REV C			
-				RESTRICTED TO			